

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761665

Luminaire Tested: LD6D15D010-EU6DR600215IC9035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR600215IC9035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1478.5 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761665

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P761665

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191851
5°	196565
10°	198949
15°	189524
20°	167096
25°	135155
30°	91418
35°	45817
40°	7431
45°	7278
50°	7428
55°	7524
60°	7736
65°	7911
70°	8114
75°	8190
80°	7865
85°	6644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 8190 cd/sqm



TEST NUMBER: P761665

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.3	11.6
10°-20°	463.5	31.3
20°-30°	498.6	33.7
30°-40°	216.8	14.7
40°-50°	36.4	2.5
50°-60°	35.4	2.4
60°-70°	30.3	2.0
70°-80°	20.2	1.4
80°-90°	6.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1133.4	76.7
0°-40°	1350.1	91.3
0°-60°	1422.0	96.2
0°-90°	1478.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1478.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1756	
5°	1792	171
15°	1676	463
25°	1121	499
35°	344	217
45°	47	36
55°	40	35
65°	31	30
75°	19	20
85°	5	6
90°	0	



TEST NUMBER: P761665

CATALOG NUMBER: LD6D15D010-EU6DR600215IC9035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1755.9
2.5°	1805.3
5°	1792.2
7.5°	1796.4
10°	1793.2
12.5°	1756.2
15°	1675.5
17.5°	1567.2
20°	1437.1
22.5°	1298.0
25°	1121.1
27.5°	896.7
30°	724.6
32.5°	558.5
35°	343.5
37.5°	147.0
40°	52.1
42.5°	48.0
45°	47.1
47.5°	45.5
50°	43.7
52.5°	41.6
55°	39.5
57.5°	37.5
60°	35.4
62.5°	33.1
65°	30.6
67.5°	28.1
70°	25.4
72.5°	22.4
75°	19.4
77.5°	16.0
80°	12.5
82.5°	8.9
85°	5.3
87.5°	1.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)