

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761742

Luminaire Tested: LD6D15D010-EU6DR650215IC9035-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9035-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1359.9 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761742

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P761742

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72111
5°	71929
10°	71866
15°	69655
20°	63414
25°	55259
30°	45960
35°	36419
40°	26280
45°	16602
50°	8659
55°	4602
60°	2418
65°	1327
70°	564
75°	632
80°	437
85°	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16602 cd/sqm



TEST NUMBER: P761742

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	8.6
10°-20°	319.8	23.5
20°-30°	390.8	28.7
30°-40°	317.1	23.3
40°-50°	158.0	11.6
50°-60°	44.1	3.2
60°-70°	10.0	0.7
70°-80°	2.6	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.4	60.8
0°-40°	1144.5	84.2
0°-60°	1346.6	99.0
0°-90°	1359.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1359.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1235	
5°	1227	117
15°	1152	320
25°	858	391
35°	511	317
45°	201	158
55°	45	44
65°	10	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P761742

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1234.7
2.5°	1233.8
5°	1226.9
7.5°	1222.9
10°	1211.8
12.5°	1189.4
15°	1152.0
17.5°	1093.6
20°	1020.3
22.5°	941.1
25°	857.5
27.5°	768.0
30°	681.5
32.5°	596.0
35°	510.8
37.5°	425.6
40°	344.7
42.5°	268.9
45°	201.0
47.5°	140.1
50°	95.3
52.5°	65.7
55°	45.2
57.5°	30.5
60°	20.7
62.5°	14.3
65°	9.6
67.5°	4.9
70°	3.3
72.5°	3.1
75°	2.8
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)