

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761743

Luminaire Tested: LD6D15D010-EU6DR650215IC9035-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9035-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1427.9 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761743

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P761743

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	97	95	94	93	93				
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85				
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78				
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72				
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66				
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61				
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56				
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52				
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49				
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75721
5°	75529
10°	75465
15°	73137
20°	66577
25°	58023
30°	48259
35°	38237
40°	27599
45°	17436
50°	9086
55°	4826
60°	2535
65°	1396
70°	581
75°	654
80°	437
85°	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17436 cd/sqm



TEST NUMBER: P761743

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.6	8.6
10°-20°	335.7	23.5
20°-30°	410.4	28.7
30°-40°	333.0	23.3
40°-50°	165.9	11.6
50°-60°	46.3	3.2
60°-70°	10.5	0.7
70°-80°	2.8	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	868.7	60.8
0°-40°	1201.7	84.2
0°-60°	1413.9	99.0
0°-90°	1427.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1296	
5°	1288	123
15°	1210	336
25°	900	410
35°	536	333
45°	211	166
55°	47	46
65°	10	11
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P761743

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9035-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1296.5
2.5°	1295.5
5°	1288.3
7.5°	1284.1
10°	1272.5
12.5°	1248.9
15°	1209.6
17.5°	1148.3
20°	1071.2
22.5°	988.2
25°	900.4
27.5°	806.4
30°	715.6
32.5°	625.8
35°	536.3
37.5°	447.0
40°	362.0
42.5°	282.4
45°	211.1
47.5°	147.1
50°	100.0
52.5°	69.0
55°	47.4
57.5°	32.0
60°	21.7
62.5°	15.1
65°	10.1
67.5°	5.2
70°	3.4
72.5°	3.3
75°	2.9
77.5°	1.9
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)