

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761761

Luminaire Tested: LD6D15D010-EU6DR650215IC9050-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 977.3 lumens
Efficiency: N/A
Efficacy: 61.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761761

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P761761

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105131
5°	105214
10°	108927
15°	109099
20°	100448
25°	85583
30°	65517
35°	46284
40°	27314
45°	11094
50°	4029
55°	2229
60°	1289
65°	724
70°	735
75°	591
80°	629
85°	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11094 cd/sqm



TEST NUMBER: P761761

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.7	9.5
10°-20°	267.3	27.3
20°-30°	320.6	32.8
30°-40°	215.5	22.0
40°-50°	64.5	6.6
50°-60°	11.4	1.2
60°-70°	3.3	0.3
70°-80°	1.6	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.5	69.6
0°-40°	896.0	91.7
0°-60°	971.9	99.5
0°-90°	977.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	977.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	962	
5°	959	93
15°	964	267
25°	710	321
35°	347	215
45°	72	65
55°	12	11
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P761761

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	962.2
2.5°	966.3
5°	959.3
7.5°	973.8
10°	981.8
12.5°	979.8
15°	964.5
17.5°	927.0
20°	863.9
22.5°	789.5
25°	709.9
27.5°	620.0
30°	519.3
32.5°	428.0
35°	347.0
37.5°	267.1
40°	191.5
42.5°	125.1
45°	71.8
47.5°	38.0
50°	23.7
52.5°	16.4
55°	11.7
57.5°	8.5
60°	5.9
62.5°	3.8
65°	2.8
67.5°	2.5
70°	2.3
72.5°	1.8
75°	1.4
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.4
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)