

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761817

Luminaire Tested: LD6D15D010-EU6DR700215IC9035-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761817
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR700215IC9035-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1644.9 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761817

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P761817

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100				
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	97	95	94	93	93				
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85				
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	78				
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71	71				
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	65				
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	60				
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56	56				
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51				
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48	48				
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44	44				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141842
5°	141496
10°	141190
15°	141145
20°	139772
25°	131297
30°	117054
35°	93328
40°	61973
45°	37053
50°	19208
55°	10096
60°	3562
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37053 cd/sqm



TEST NUMBER: P761817

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	7.5
10°-20°	351.9	21.4
20°-30°	496.4	30.2
30°-40°	428.5	26.1
40°-50°	191.9	11.7
50°-60°	50.2	3.1
60°-70°	3.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	970.9	59.0
0°-40°	1399.5	85.1
0°-60°	1641.6	99.8
0°-90°	1644.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1644.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1298	
5°	1290	123
15°	1248	352
25°	1089	496
35°	700	429
45°	240	192
55°	53	50
65°	0	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761817

CATALOG NUMBER: LD6D15D010-EU6DR700215IC9035-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1298.2
2.5°	1296.9
5°	1290.1
7.5°	1284.5
10°	1272.6
12.5°	1261.9
15°	1247.8
17.5°	1231.7
20°	1202.1
22.5°	1153.3
25°	1089.1
27.5°	1014.6
30°	927.8
32.5°	821.6
35°	699.7
37.5°	565.2
40°	434.5
42.5°	330.1
45°	239.8
47.5°	165.3
50°	113.0
52.5°	78.0
55°	53.0
57.5°	32.0
60°	16.3
62.5°	5.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)