

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761298

Luminaire Tested: LD6D15D010-EU6DR350215IC9040-6LBDP1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761298  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR350215IC9040-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1519.5 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761298

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9040-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P761298

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9040-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 |  | 103 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 99  | 102 | 99  | 97  |  | 99  | 97  | 95  |  | 96  |
| 3   | 106 | 101 | 97  | 94  | 105 | 100 | 96  | 93  | 97  | 95  | 92  |  | 95  | 93  | 91  |  | 93  |
| 4   | 103 | 97  | 92  | 89  | 101 | 96  | 92  | 89  | 94  | 90  | 88  |  | 92  | 89  | 87  |  | 90  |
| 5   | 99  | 93  | 88  | 85  | 98  | 92  | 87  | 84  | 90  | 86  | 84  |  | 89  | 85  | 83  |  | 87  |
| 6   | 96  | 89  | 84  | 81  | 94  | 88  | 84  | 81  | 87  | 83  | 80  |  | 85  | 82  | 80  |  | 84  |
| 7   | 93  | 85  | 81  | 78  | 91  | 85  | 80  | 77  | 84  | 80  | 77  |  | 83  | 79  | 77  |  | 82  |
| 8   | 90  | 82  | 78  | 74  | 88  | 82  | 77  | 74  | 81  | 77  | 74  |  | 80  | 76  | 74  |  | 79  |
| 9   | 87  | 79  | 75  | 72  | 86  | 79  | 75  | 72  | 78  | 74  | 71  |  | 77  | 74  | 71  |  | 77  |
| 10  | 84  | 77  | 72  | 69  | 83  | 76  | 72  | 69  | 76  | 72  | 69  |  | 75  | 71  | 69  |  | 74  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 456808 |
| 5°  | 446072 |
| 10° | 402036 |
| 15° | 312039 |
| 20° | 176991 |
| 25° | 68862  |
| 30° | 25687  |
| 35° | 14085  |
| 40° | 9200   |
| 45° | 5609   |
| 50° | 3570   |
| 55° | 2514   |
| 60° | 1836   |
| 65° | 1008   |
| 70° | 64     |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5609 cd/sqm



TEST NUMBER: P761298

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9040-6LBDP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 374.1  | 24.6      |
| 10°-20°   | 730.3  | 48.1      |
| 20°-30°   | 297.9  | 19.6      |
| 30°-40°   | 71.3   | 4.7       |
| 40°-50°   | 29.7   | 2.0       |
| 50°-60°   | 12.3   | 0.8       |
| 60°-70°   | 3.8    | 0.3       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1402.2 | 92.3      |
| 0°-40°    | 1473.5 | 97.0      |
| 0°-60°    | 1515.6 | 99.7      |
| 0°-90°    | 1519.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1519.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4181 |      |
| 5°  | 4067 | 374  |
| 15° | 2759 | 730  |
| 25° | 571  | 298  |
| 35° | 106  | 71   |
| 45° | 36   | 30   |
| 55° | 13   | 12   |
| 65° | 4    | 4    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P761298

CATALOG NUMBER: LD6D15D010-EU6DR350215IC9040-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4180.9 |
| 2.5°  | 4155.8 |
| 5°    | 4067.1 |
| 7.5°  | 3890.2 |
| 10°   | 3623.7 |
| 12.5° | 3248.4 |
| 15°   | 2758.6 |
| 17.5° | 2159.7 |
| 20°   | 1522.2 |
| 22.5° | 970.6  |
| 25°   | 571.2  |
| 27.5° | 322.9  |
| 30°   | 203.6  |
| 32.5° | 143.0  |
| 35°   | 105.6  |
| 37.5° | 81.6   |
| 40°   | 64.5   |
| 42.5° | 49.7   |
| 45°   | 36.3   |
| 47.5° | 27.2   |
| 50°   | 21.0   |
| 52.5° | 16.7   |
| 55°   | 13.2   |
| 57.5° | 10.7   |
| 60°   | 8.4    |
| 62.5° | 6.1    |
| 65°   | 3.9    |
| 67.5° | 1.4    |
| 70°   | 0.2    |
| 72.5° | 0.2    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.2    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)