

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761892

Luminaire Tested: LD6D20D010-EU6DR1015209035-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR1015209035-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2109.5 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761892

CATALOG NUMBER: LD6D20D010-EU6DR1015209035-6LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P761892

CATALOG NUMBER: LD6D20D010-EU6DR1015209035-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	113	111	114	112	111	109		108	107	106		104	104	103		101	101	100
2	113	110	108	106	111	108	106	104		105	104	102		103	101	100		100	99	98
3	111	107	104	102	109	106	103	101		103	101	99		101	99	98		99	98	96
4	108	104	101	99	107	103	100	98		101	99	97		99	97	96		98	96	95
5	106	102	99	96	105	101	98	96		99	97	95		98	96	94		97	95	94
6	104	100	96	94	103	99	96	94		98	95	93		97	94	93		96	94	92
7	103	98	95	93	102	97	94	92		96	94	92		95	93	92		95	93	91
8	101	96	93	91	100	96	93	91		95	92	91		94	92	90		93	92	90
9	100	95	92	90	99	94	92	90		94	91	90		93	91	89		93	91	89
10	98	94	91	89	98	93	91	89		93	90	88		92	90	88		92	90	88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5018609
5°	2379807
10°	488064
15°	133996
20°	53997
25°	28933
30°	17120
35°	11137
40°	7445
45°	4836
50°	2669
55°	1981
60°	1136
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4836 cd/sqm

TEST NUMBER: P761892

CATALOG NUMBER: LD6D20D010-EU6DR1015209035-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1500.0	71.1
10°-20°	405.9	19.2
20°-30°	116.2	5.5
30°-40°	53.1	2.5
40°-50°	24.3	1.2
50°-60°	8.1	0.4
60°-70°	1.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2022.1	95.9
0°-40°	2075.2	98.4
0°-60°	2107.6	99.9
0°-90°	2109.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2109.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	45932	
5°	21698	###
15°	1185	406
25°	240	116
35°	84	53
45°	31	24
55°	10	8
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761892

CATALOG NUMBER: LD6D20D010-EU6DR1015209035-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	45932.4
0.5°	45535.8
1°	44518.2
1.5°	42556.1
2°	40359.2
2.5°	37457.7
3°	34232.8
3.5°	31112.2
4°	27746.3
4.5°	24646.5
5°	21698.1
5.5°	19026.3
6°	16479.7
6.5°	14241.0
7°	12132.8
7.5°	10332.4
8°	8735.6
8.5°	7337.1
9°	6126.4
9.5°	5202.8
10°	4399.1
12.5°	2097.8
15°	1184.6
17.5°	720.1
20°	464.4
22.5°	323.5
25°	240.0
27.5°	177.4
30°	135.7
32.5°	104.4
35°	83.5
37.5°	62.6
40°	52.2
42.5°	41.7
45°	31.3
47.5°	20.9
50°	15.7
52.5°	10.4
55°	10.4
57.5°	5.2
60°	5.2
62.5°	5.2
65°	0.0



TEST NUMBER: P761892

CATALOG NUMBER: LD6D20D010-EU6DR1015209035-6LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	0.0
70°	0.0



(END OF REPORT)