

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762069

Luminaire Tested: LD6D20D010-EU6DR2015309050-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR2015309050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1867.5 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762069

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P762069

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		113	111	109	108		107	106	104		103	102	101		100	99	98
2	111	108	105	102		109	106	104	101		103	101	99		100	99	97		98	96	95
3	108	103	100	97		106	102	99	96		100	97	95		97	95	93		95	93	92
4	105	99	96	93		103	98	95	92		96	93	91		95	92	90		93	91	89
5	102	96	92	89		100	95	91	89		94	90	88		92	89	87		91	88	86
6	99	93	89	86		98	92	88	86		91	87	85		90	87	84		88	86	84
7	96	90	86	83		95	89	86	83		88	85	82		87	84	82		86	84	82
8	94	87	83	81		93	87	83	80		86	83	80		85	82	80		84	82	80
9	91	85	81	78		91	85	81	78		84	80	78		83	80	78		82	80	78
10	89	83	79	76		88	82	79	76		82	78	76		81	78	76		81	78	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1161398
5°	1047799
10°	588082
15°	298929
20°	126563
25°	58421
30°	30935
35°	16660
40°	8914
45°	5269
50°	3060
55°	1619
60°	1027
65°	724
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5269 cd/sqm



TEST NUMBER: P762069

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	756.8	40.5
10°-20°	745.2	39.9
20°-30°	243.5	13.0
30°-40°	82.9	4.4
40°-50°	27.9	1.5
50°-60°	8.4	0.4
60°-70°	2.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1745.5	93.5
0°-40°	1828.4	97.9
0°-60°	1864.6	99.8
0°-90°	1867.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1867.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10630	
5°	9553	757
15°	2643	745
25°	485	243
35°	125	83
45°	34	28
55°	8	8
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762069

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10629.6
0.5°	10629.6
1°	10616.4
1.5°	10589.9
2°	10541.6
2.5°	10477.2
3°	10386.3
3.5°	10259.5
4°	10071.1
4.5°	9842.1
5°	9553.4
5.5°	9173.8
6°	8784.8
6.5°	8339.0
7°	7902.6
7.5°	7391.5
8°	6935.3
8.5°	6476.2
9°	6052.2
9.5°	5663.1
10°	5300.6
12.5°	3806.0
15°	2642.7
17.5°	1726.5
20°	1088.5
22.5°	705.2
25°	484.6
27.5°	340.8
30°	245.2
32.5°	176.1
35°	124.9
37.5°	87.1
40°	62.5
42.5°	45.4
45°	34.1
47.5°	26.5
50°	18.0
52.5°	11.4
55°	8.5
57.5°	6.6
60°	4.7
62.5°	3.8
65°	2.8



TEST NUMBER: P762069

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	1.9
70°	0.9



(END OF REPORT)