

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761751

Luminaire Tested: LD6D15D010-EU6DR650215IC9040-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1145.5 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761751

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P761751

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	83	78	73		90	83	77	73		81	76	72		79	75	72		77	74	71
6	87	78	72	68		86	77	72	68		76	71	67		74	70	67		73	69	66
7	83	73	67	63		81	73	67	63		71	66	62		70	66	62		69	65	62
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	58	55		63	58	55		62	58	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123224
5°	123322
10°	127666
15°	127877
20°	117726
25°	100315
30°	76796
35°	54247
40°	32020
45°	13010
50°	4708
55°	2629
60°	1508
65°	827
70°	894
75°	675
80°	692
85°	627

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13010 cd/sqm



TEST NUMBER: P761751

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.6	9.5
10°-20°	313.2	27.3
20°-30°	375.8	32.8
30°-40°	252.6	22.0
40°-50°	75.6	6.6
50°-60°	13.4	1.2
60°-70°	3.8	0.3
70°-80°	1.9	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.7	69.6
0°-40°	1050.2	91.7
0°-60°	1139.2	99.5
0°-90°	1145.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1145.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1128	
5°	1124	109
15°	1130	313
25°	832	376
35°	407	253
45°	84	76
55°	14	13
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P761751

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1127.8
2.5°	1132.6
5°	1124.4
7.5°	1141.4
10°	1150.7
12.5°	1148.4
15°	1130.5
17.5°	1086.6
20°	1012.5
22.5°	925.4
25°	832.1
27.5°	726.8
30°	608.7
32.5°	501.6
35°	406.7
37.5°	313.0
40°	224.5
42.5°	146.6
45°	84.2
47.5°	44.6
50°	27.7
52.5°	19.3
55°	13.8
57.5°	9.9
60°	6.9
62.5°	4.5
65°	3.2
67.5°	2.9
70°	2.8
72.5°	2.1
75°	1.6
77.5°	1.4
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)