

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761753

Luminaire Tested: LD6D15D010-EU6DR650215IC9040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1397.5 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761753

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P761753

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74109
5°	73917
10°	73858
15°	71577
20°	65160
25°	56786
30°	47234
35°	37424
40°	27012
45°	17064
50°	8895
55°	4725
60°	2488
65°	1368
70°	581
75°	632
80°	437
85°	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17064 cd/sqm

TEST NUMBER: P761753

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.0	8.6
10°-20°	328.6	23.5
20°-30°	401.7	28.7
30°-40°	325.9	23.3
40°-50°	162.4	11.6
50°-60°	45.3	3.2
60°-70°	10.3	0.7
70°-80°	2.7	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.2	60.8
0°-40°	1176.1	84.2
0°-60°	1383.8	99.0
0°-90°	1397.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1397.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1269	
5°	1261	120
15°	1184	329
25°	881	402
35°	525	326
45°	207	162
55°	46	45
65°	10	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P761753

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9040-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1268.9
2.5°	1267.9
5°	1260.8
7.5°	1256.8
10°	1245.4
12.5°	1222.3
15°	1183.8
17.5°	1123.8
20°	1048.4
22.5°	967.2
25°	881.2
27.5°	789.3
30°	700.4
32.5°	612.5
35°	524.9
37.5°	437.4
40°	354.3
42.5°	276.3
45°	206.6
47.5°	143.9
50°	97.9
52.5°	67.5
55°	46.4
57.5°	31.3
60°	21.3
62.5°	14.7
65°	9.9
67.5°	5.0
70°	3.4
72.5°	3.2
75°	2.8
77.5°	1.9
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)