

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762070

Luminaire Tested: LD6D20D010-EU6DR2015309050-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR2015309050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2178.6 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762070

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P762070

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		113	111	109	108		107	106	104		103	102	101		100	99	98
2	111	108	105	102		109	106	104	101		103	101	99		100	99	97		98	96	95
3	108	103	100	97		106	102	99	96		100	97	95		97	95	93		95	93	92
4	105	99	96	93		103	98	95	92		96	93	91		95	92	90		93	91	89
5	102	96	92	89		100	95	91	89		94	90	88		92	89	87		91	88	86
6	99	93	89	86		98	92	88	86		91	87	85		90	87	84		88	86	84
7	96	90	86	83		95	89	86	83		88	85	82		87	84	82		86	84	82
8	94	87	83	81		93	87	83	80		86	83	80		85	82	80		84	82	80
9	91	85	81	78		91	85	81	78		84	80	78		83	80	78		82	80	78
10	89	83	79	76		88	82	79	76		82	78	76		81	78	76		81	78	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1354855
5°	1222330
10°	686036
15°	348722
20°	147643
25°	68162
30°	36083
35°	19447
40°	10398
45°	6150
50°	3570
55°	1886
60°	1202
65°	853
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6150 cd/sqm



TEST NUMBER: P762070

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	882.9	40.5
10°-20°	869.3	39.9
20°-30°	284.0	13.0
30°-40°	96.7	4.4
40°-50°	32.5	1.5
50°-60°	9.8	0.4
60°-70°	3.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2036.2	93.5
0°-40°	2132.9	97.9
0°-60°	2175.2	99.8
0°-90°	2178.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2178.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12400	
5°	11145	883
15°	3083	869
25°	565	284
35°	146	97
45°	40	33
55°	10	10
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762070

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	12400.2
0.5°	12400.2
1°	12384.7
1.5°	12353.8
2°	12297.5
2.5°	12222.4
3°	12116.4
3.5°	11968.4
4°	11748.7
4.5°	11481.5
5°	11144.7
5.5°	10701.9
6°	10248.1
6.5°	9728.0
7°	9219.0
7.5°	8622.7
8°	8090.5
8.5°	7554.9
9°	7060.3
9.5°	6606.4
10°	6183.5
12.5°	4440.0
15°	3082.9
17.5°	2014.1
20°	1269.8
22.5°	822.6
25°	565.4
27.5°	397.5
30°	286.0
32.5°	205.4
35°	145.8
37.5°	101.6
40°	72.9
42.5°	53.0
45°	39.8
47.5°	30.9
50°	21.0
52.5°	13.3
55°	9.9
57.5°	7.7
60°	5.5
62.5°	4.4
65°	3.3



TEST NUMBER: P762070

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBDP1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	2.2
70°	1.1



(END OF REPORT)