

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763906

Luminaire Tested: LD6D30D010-EU6DR2015309030-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D30D010-EU6DR2015309030-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3326.6 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763906

CATALOG NUMBER: LD6D30D010-EU6DR2015309030-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P763906

CATALOG NUMBER: LD6D30D010-EU6DR2015309030-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2068787
5°	1866425
10°	1047544
15°	532489
20°	225453
25°	104076
30°	55096
35°	29691
40°	15875
45°	9379
50°	5439
55°	2895
60°	1836
65°	1319
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9379 cd/sqm



TEST NUMBER: P763906

CATALOG NUMBER: LD6D30D010-EU6DR2015309030-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1348.1	40.5
10°-20°	1327.5	39.9
20°-30°	433.7	13.0
30°-40°	147.7	4.4
40°-50°	49.6	1.5
50°-60°	14.9	0.4
60°-70°	5.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3109.2	93.5
0°-40°	3256.9	97.9
0°-60°	3321.4	99.8
0°-90°	3326.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3326.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18934	
5°	17017	###
15°	4708	1327
25°	863	434
35°	223	148
45°	61	50
55°	15	15
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P763906

CATALOG NUMBER: LD6D30D010-EU6DR2015309030-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	18934.4
0.5°	18934.4
1°	18910.8
1.5°	18863.6
2°	18777.6
2.5°	18662.9
3°	18501.1
3.5°	18275.1
4°	17939.6
4.5°	17531.6
5°	17017.3
5.5°	16341.2
6°	15648.3
6.5°	14854.1
7°	14076.9
7.5°	13166.4
8°	12353.7
8.5°	11536.0
9°	10780.6
9.5°	10087.7
10°	9441.9
12.5°	6779.6
15°	4707.5
17.5°	3075.4
20°	1939.0
22.5°	1256.1
25°	863.3
27.5°	607.0
30°	436.7
32.5°	313.6
35°	222.6
37.5°	155.1
40°	111.3
42.5°	80.9
45°	60.7
47.5°	47.2
50°	32.0
52.5°	20.2
55°	15.2
57.5°	11.8
60°	8.4
62.5°	6.7
65°	5.1



TEST NUMBER: P763906

CATALOG NUMBER: LD6D30D010-EU6DR2015309030-6LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	3.4
70°	1.7



(END OF REPORT)