

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761385

Luminaire Tested: LD6D15D010-EU6DR400215IC9050-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR400215IC9050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1393.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761385

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P761385

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96						
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88						
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84						
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81						
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77						
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74						
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72						
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69						
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	354354
5°	352626
10°	333316
15°	283365
20°	193129
25°	80580
30°	25334
35°	11778
40°	6518
45°	2982
50°	1445
55°	800
60°	415
65°	155
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2982 cd/sqm



TEST NUMBER: P761385

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.2	21.6
10°-20°	672.6	48.3
20°-30°	336.7	24.2
30°-40°	61.7	4.4
40°-50°	17.0	1.2
50°-60°	4.0	0.3
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1309.4	94.0
0°-40°	1371.2	98.4
0°-60°	1392.2	99.9
0°-90°	1393.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1393.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3243	
5°	3215	300
15°	2505	673
25°	668	337
35°	88	62
45°	19	17
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761385

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3243.2
2.5°	3238.4
5°	3215.1
7.5°	3140.9
10°	3004.3
12.5°	2791.3
15°	2505.1
17.5°	2132.8
20°	1661.0
22.5°	1132.4
25°	668.4
27.5°	353.3
30°	200.8
32.5°	129.8
35°	88.3
37.5°	63.1
40°	45.7
42.5°	31.3
45°	19.3
47.5°	12.3
50°	8.5
52.5°	6.1
55°	4.2
57.5°	2.6
60°	1.9
62.5°	1.1
65°	0.6
67.5°	0.4
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)