

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763850

Luminaire Tested: LD6D30D010-EU6DR1515309040-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D30D010-EU6DR1515309040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3263.2 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763850

CATALOG NUMBER: LD6D30D010-EU6DR1515309040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P763850

CATALOG NUMBER: LD6D30D010-EU6DR1515309040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101
2	113	110	107	105	111	108	106	104	105	103	102		102	101	100		100
3	110	106	103	101	108	105	102	100	103	100	99		100	99	97		98
4	108	103	100	98	106	102	99	97	100	98	96		99	97	95		97
5	106	101	98	95	104	100	97	95	98	96	94		97	95	93		96
6	104	99	95	93	102	98	95	93	97	94	92		96	93	92		95
7	102	97	94	91	101	96	93	91	95	93	91		94	92	90		93
8	100	95	92	90	99	95	92	90	94	91	89		93	91	89		92
9	99	93	90	88	98	93	90	88	92	90	88		92	89	88		91
10	97	92	89	87	96	92	89	87	91	89	87		91	88	87		90

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5002738	5002738	5002738
5°	2939850	2901780	2924738
10°	877409	883558	897078
15°	218245	222501	215631
20°	65295	75621	66686
25°	23020	29322	23316
30°	8454	11135	8596
35°	4234	4786	4103
40°	2670	2940	2670
45°	1974	2107	1974
50°	1572	1572	1572
55°	1309	1309	1309
60°	1060	1060	1060
65°	806	806	806
70°	687	687	687
75°	423	423	567
80°	300	300	300
85°	158	158	158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 2107 cd/sqm



TEST NUMBER: P763850

CATALOG NUMBER: LD6D30D010-EU6DR1515309040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2116.4	64.9
10°-20°	870.5	26.7
20°-30°	172.9	5.3
30°-40°	43.2	1.3
40°-50°	22.7	0.7
50°-60°	16.8	0.5
60°-70°	11.9	0.4
70°-80°	6.7	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3159.9	96.8
0°-40°	3203.0	98.2
0°-60°	3242.5	99.4
0°-90°	3263.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3263.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	44461	44461	44461	44461	44461	
5°	28927	28630	28553	28750	28779	2112
15°	2513	2560	2562	2516	2483	861
25°	296	335	376	333	299	155
35°	58	62	66	62	56	40
45°	28	28	30	28	28	22
55°	19	19	19	19	19	17
65°	11	11	11	11	11	12
75°	6	6	6	6	8	7
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P763850

CATALOG NUMBER: LD6D30D010-EU6DR1515309040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	44460.9	44460.9	44460.9	44460.9	44460.9
2.5°	40105.5	40139.4	40152.6	40192.1	40338.9
5°	28927.3	28629.9	28552.7	28750.3	28778.6
7.5°	17135.4	17195.6	17415.8	17464.8	17287.8
10°	9403.4	9480.6	9469.3	9537.0	9614.2
12.5°	4809.0	4748.7	4729.9	4807.1	4699.8
15°	2512.7	2559.8	2561.7	2516.5	2482.6
17.5°	1351.4	1406.0	1496.3	1422.9	1310.0
20°	798.0	847.0	924.2	863.9	815.0
22.5°	493.1	532.7	587.2	540.2	500.7
25°	295.5	335.0	376.4	333.1	299.3
27.5°	175.0	208.9	235.3	207.0	173.2
30°	112.9	131.8	148.7	129.9	114.8
32.5°	79.1	86.6	94.1	86.6	79.1
35°	58.3	62.1	65.9	62.1	56.5
37.5°	45.2	48.9	50.8	47.1	43.3
40°	37.6	39.5	41.4	39.5	37.6
42.5°	32.0	33.9	33.9	33.9	32.0
45°	28.2	28.2	30.1	28.2	28.2
47.5°	24.5	24.5	26.4	24.5	24.5
50°	22.6	22.6	22.6	22.6	22.6
52.5°	20.7	20.7	20.7	20.7	20.7
55°	18.8	18.8	18.8	18.8	18.8
57.5°	16.9	16.9	16.9	16.9	16.9
60°	15.1	15.1	15.1	15.1	15.1
62.5°	13.2	13.2	13.2	13.2	13.2
65°	11.3	11.3	11.3	11.3	11.3
67.5°	11.3	11.3	11.3	11.3	11.3
70°	9.4	9.4	9.4	9.4	9.4
72.5°	7.5	7.5	7.5	7.5	7.5
75°	5.6	5.6	5.6	5.6	5.6
77.5°	5.6	5.6	5.6	5.6	5.6
80°	3.8	3.8	3.8	3.8	3.8
82.5°	3.8	3.8	3.8	3.8	3.8
85°	1.9	1.9	1.9	1.9	1.9
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)