

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761390

Luminaire Tested: LD6D15D010-EU6DR400215IC9050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR400215IC9050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1645.3 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761390

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P761390

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	418534
5°	416503
10°	393693
15°	334685
20°	228104
25°	95179
30°	29926
35°	13912
40°	7688
45°	3523
50°	1717
55°	933
60°	481
65°	181
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3523 cd/sqm

TEST NUMBER: P761390

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.6	21.6
10°-20°	794.4	48.3
20°-30°	397.6	24.2
30°-40°	72.9	4.4
40°-50°	20.1	1.2
50°-60°	4.7	0.3
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1546.6	94.0
0°-40°	1619.5	98.4
0°-60°	1644.4	99.9
0°-90°	1645.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1645.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3831	
5°	3798	355
15°	2959	794
25°	790	398
35°	104	73
45°	23	20
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P761390

CATALOG NUMBER: LD6D15D010-EU6DR400215IC9050-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3830.6
2.5°	3825.0
5°	3797.5
7.5°	3709.8
10°	3548.5
12.5°	3296.9
15°	2958.8
17.5°	2519.1
20°	1961.8
22.5°	1337.5
25°	789.5
27.5°	417.3
30°	237.2
32.5°	153.3
35°	104.3
37.5°	74.5
40°	53.9
42.5°	36.9
45°	22.8
47.5°	14.6
50°	10.1
52.5°	7.2
55°	4.9
57.5°	3.2
60°	2.2
62.5°	1.3
65°	0.7
67.5°	0.5
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)