

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763864

Luminaire Tested: LD6D30D010-EU6DR1515309050-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D30D010-EU6DR1515309050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3450.8 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763864

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P763864

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111	113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105	111	108	106	104		105	103	102		102	101	100		100	98	98
3	110	106	103	101	108	105	102	100		103	100	99		100	99	97		98	97	96
4	108	103	100	98	106	102	99	97		100	98	96		99	97	95		97	95	94
5	106	101	98	95	104	100	97	95		98	96	94		97	95	93		96	94	92
6	104	99	95	93	102	98	95	93		97	94	92		96	93	92		95	93	91
7	102	97	94	91	101	96	93	91		95	93	91		94	92	90		93	91	90
8	100	95	92	90	99	95	92	90		94	91	89		93	91	89		92	90	89
9	99	93	90	88	98	93	90	88		92	90	88		92	89	88		91	89	88
10	97	92	89	87	96	92	89	87		91	89	87		91	88	87		90	88	86

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5290170	5290170	5290170
5°	3108747	3068502	3092771
10°	927813	934317	948621
15°	230787	235278	228017
20°	69050	79957	70515
25°	24344	31012	24656
30°	8941	11771	9091
35°	4481	5062	4335
40°	2826	3110	2826
45°	2093	2226	2093
50°	1662	1662	1662
55°	1385	1385	1385
60°	1116	1116	1116
65°	849	849	849
70°	731	731	731
75°	454	454	605
80°	315	315	315
85°	166	166	166

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 2226 cd/sqm



TEST NUMBER: P763864

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2238.0	64.9
10°-20°	920.6	26.7
20°-30°	182.8	5.3
30°-40°	45.6	1.3
40°-50°	24.0	0.7
50°-60°	17.8	0.5
60°-70°	12.5	0.4
70°-80°	7.2	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3341.4	96.8
0°-40°	3387.1	98.2
0°-60°	3428.9	99.4
0°-90°	3450.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3450.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	47015	47015	47015	47015	47015	
5°	30589	30275	30193	30402	30432	2234
15°	2657	2707	2709	2661	2625	911
25°	312	354	398	352	316	164
35°	62	66	70	66	60	42
45°	30	30	32	30	30	23
55°	20	20	20	20	20	18
65°	12	12	12	12	12	13
75°	6	6	6	6	8	7
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P763864

CATALOG NUMBER: LD6D30D010-EU6DR1515309050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	47015.4	47015.4	47015.4	47015.4	47015.4
2.5°	42409.8	42445.6	42459.5	42501.3	42656.6
5°	30589.2	30274.8	30193.2	30402.2	30432.0
7.5°	18119.9	18183.6	18416.4	18468.2	18281.1
10°	9943.6	10025.2	10013.3	10085.0	10166.6
12.5°	5085.3	5021.6	5001.7	5083.3	4969.8
15°	2657.1	2706.8	2708.8	2661.1	2625.2
17.5°	1429.1	1486.8	1582.3	1504.7	1385.3
20°	843.9	895.6	977.2	913.6	861.8
22.5°	521.5	563.3	621.0	571.2	529.4
25°	312.5	354.3	398.1	352.3	316.5
27.5°	185.1	220.9	248.8	218.9	183.1
30°	119.4	139.3	157.2	137.3	121.4
32.5°	83.6	91.6	99.5	91.6	83.6
35°	61.7	65.7	69.7	65.7	59.7
37.5°	47.8	51.7	53.7	49.8	45.8
40°	39.8	41.8	43.8	41.8	39.8
42.5°	33.8	35.8	35.8	35.8	33.8
45°	29.9	29.9	31.8	29.9	29.9
47.5°	25.9	25.9	27.9	25.9	25.9
50°	23.9	23.9	23.9	23.9	23.9
52.5°	21.9	21.9	21.9	21.9	21.9
55°	19.9	19.9	19.9	19.9	19.9
57.5°	17.9	17.9	17.9	17.9	17.9
60°	15.9	15.9	15.9	15.9	15.9
62.5°	13.9	13.9	13.9	13.9	13.9
65°	11.9	11.9	11.9	11.9	11.9
67.5°	11.9	11.9	11.9	11.9	11.9
70°	10.0	10.0	10.0	10.0	10.0
72.5°	8.0	8.0	8.0	8.0	8.0
75°	6.0	6.0	6.0	6.0	8.0
77.5°	6.0	6.0	6.0	6.0	6.0
80°	4.0	4.0	4.0	4.0	4.0
82.5°	4.0	4.0	4.0	4.0	4.0
85°	2.0	2.0	2.0	2.0	2.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)