

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761762

Luminaire Tested: LD6D15D010-EU6DR650215IC9050-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P761762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1311.9 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761762

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P761762

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141132
5°	141243
10°	146227
15°	146461
20°	134842
25°	114890
30°	87961
35°	62143
40°	36670
45°	14896
50°	5388
55°	3010
60°	1726
65°	957
70°	990
75°	760
80°	818
85°	752

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14896 cd/sqm



TEST NUMBER: P761762

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.4	9.5
10°-20°	358.8	27.3
20°-30°	430.5	32.8
30°-40°	289.3	22.1
40°-50°	86.6	6.6
50°-60°	15.3	1.2
60°-70°	4.4	0.3
70°-80°	2.1	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	913.6	69.6
0°-40°	1202.9	91.7
0°-60°	1304.8	99.5
0°-90°	1311.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1311.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1292	
5°	1288	124
15°	1295	359
25°	953	430
35°	466	289
45°	96	87
55°	16	15
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P761762

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1291.7
2.5°	1297.2
5°	1287.8
7.5°	1307.3
10°	1318.0
12.5°	1315.4
15°	1294.8
17.5°	1244.5
20°	1159.7
22.5°	1059.8
25°	953.0
27.5°	832.4
30°	697.2
32.5°	574.6
35°	465.9
37.5°	358.5
40°	257.1
42.5°	167.9
45°	96.4
47.5°	51.0
50°	31.7
52.5°	22.0
55°	15.8
57.5°	11.4
60°	7.9
62.5°	5.2
65°	3.7
67.5°	3.3
70°	3.1
72.5°	2.4
75°	1.8
77.5°	1.7
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)