

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761766

Luminaire Tested: LD6D15D010-EU6DR650215IC9050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1381.0 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761766

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P761766

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73233
5°	73049
10°	72986
15°	70737
20°	64396
25°	56116
30°	46675
35°	36982
40°	26692
45°	16858
50°	8786
55°	4674
60°	2453
65°	1340
70°	564
75°	632
80°	437
85°	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16858 cd/sqm



TEST NUMBER: P761766

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.6	8.6
10°-20°	324.7	23.5
20°-30°	396.9	28.7
30°-40°	322.0	23.3
40°-50°	160.5	11.6
50°-60°	44.7	3.2
60°-70°	10.2	0.7
70°-80°	2.7	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	840.2	60.8
0°-40°	1162.3	84.2
0°-60°	1367.5	99.0
0°-90°	1381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1381.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1254	
5°	1246	119
15°	1170	325
25°	871	397
35°	519	322
45°	204	160
55°	46	45
65°	10	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P761766

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1253.9
2.5°	1253.0
5°	1246.0
7.5°	1241.9
10°	1230.7
12.5°	1207.8
15°	1169.9
17.5°	1110.6
20°	1036.1
22.5°	955.8
25°	870.8
27.5°	780.0
30°	692.1
32.5°	605.3
35°	518.7
37.5°	432.3
40°	350.1
42.5°	273.1
45°	204.1
47.5°	142.3
50°	96.7
52.5°	66.7
55°	45.9
57.5°	30.9
60°	21.0
62.5°	14.6
65°	9.7
67.5°	5.0
70°	3.3
72.5°	3.2
75°	2.8
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)