

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761768

Luminaire Tested: LD6D15D010-EU6DR650215IC9050-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR650215IC9050-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1312.3 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761768

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P761768

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69588
5°	69408
10°	69351
15°	67212
20°	61195
25°	53325
30°	44348
35°	35143
40°	25365
45°	16024
50°	8350
55°	4440
60°	2324
65°	1285
70°	546
75°	587
80°	404
85°	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16024 cd/sqm



TEST NUMBER: P761768

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	8.6
10°-20°	308.6	23.5
20°-30°	377.2	28.7
30°-40°	306.0	23.3
40°-50°	152.5	11.6
50°-60°	42.5	3.2
60°-70°	9.7	0.7
70°-80°	2.5	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.4	60.8
0°-40°	1104.4	84.2
0°-60°	1299.4	99.0
0°-90°	1312.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1312.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1192	
5°	1184	113
15°	1112	309
25°	828	377
35°	493	306
45°	194	153
55°	44	43
65°	9	10
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P761768

CATALOG NUMBER: LD6D15D010-EU6DR650215IC9050-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1191.5
2.5°	1190.6
5°	1183.9
7.5°	1180.1
10°	1169.4
12.5°	1147.7
15°	1111.6
17.5°	1055.3
20°	984.6
22.5°	908.2
25°	827.5
27.5°	741.2
30°	657.6
32.5°	575.2
35°	492.9
37.5°	410.7
40°	332.7
42.5°	259.5
45°	194.0
47.5°	135.2
50°	91.9
52.5°	63.4
55°	43.6
57.5°	29.4
60°	19.9
62.5°	13.8
65°	9.3
67.5°	4.8
70°	3.2
72.5°	3.0
75°	2.6
77.5°	1.8
80°	1.2
82.5°	0.9
85°	0.5
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report







(END OF REPORT)