

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770236

Luminaire Tested: LD6D70BD010-EU6DR2570959035-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR2570959035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6454.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P770236

CATALOG NUMBER: LD6D70BD010-EU6DR2570959035-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770236

CATALOG NUMBER: LD6D70BD010-EU6DR2570959035-6LB DP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82						
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77						
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2674561
5°	2491020
10°	1776904
15°	1046529
20°	651163
25°	357364
30°	163432
35°	61890
40°	28027
45°	16858
50°	7003
55°	4515
60°	3147
65°	2120
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16858 cd/sqm



TEST NUMBER: P770236

CATALOG NUMBER: LD6D70BD010-EU6DR2570959035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1951.9	30.2
10°-20°	2643.7	41.0
20°-30°	1399.0	21.7
30°-40°	345.3	5.4
40°-50°	84.3	1.3
50°-60°	22.2	0.3
60°-70°	7.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5994.7	92.9
0°-40°	6340.0	98.2
0°-60°	6446.4	99.9
0°-90°	6454.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6454.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24479	
5°	22712	###
15°	9252	2644
25°	2964	1399
35°	464	345
45°	109	84
55°	24	22
65°	8	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P770236

CATALOG NUMBER: LD6D70BD010-EU6DR2570959035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	24478.7
2.5°	24076.4
5°	22712.1
7.5°	19971.1
10°	16015.9
12.5°	12107.1
15°	9251.9
17.5°	7210.6
20°	5600.3
22.5°	4200.0
25°	2964.3
27.5°	1987.8
30°	1295.4
32.5°	788.1
35°	464.0
37.5°	284.0
40°	196.5
42.5°	150.2
45°	109.1
47.5°	65.8
50°	41.2
52.5°	29.8
55°	23.7
57.5°	18.5
60°	14.4
62.5°	11.3
65°	8.2
67.5°	3.1
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)