

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762005

Luminaire Tested: LD6D20D010-EU6DR2015309024-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR2015309024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1772.9 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762005

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P762005

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1102550
5°	994715
10°	558282
15°	283783
20°	120156
25°	55468
30°	29358
35°	15819
40°	8458
45°	4991
50°	2907
55°	1543
60°	983
65°	698
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4991 cd/sqm



TEST NUMBER: P762005

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	718.5	40.5
10°-20°	707.5	39.9
20°-30°	231.1	13.0
30°-40°	78.7	4.4
40°-50°	26.5	1.5
50°-60°	8.0	0.5
60°-70°	2.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1657.0	93.5
0°-40°	1735.7	97.9
0°-60°	1770.2	99.8
0°-90°	1772.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1772.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10091	
5°	9069	718
15°	2509	707
25°	460	231
35°	119	79
45°	32	26
55°	8	8
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762005

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	10091.0
0.5°	10091.0
1°	10078.5
1.5°	10053.3
2°	10007.5
2.5°	9946.4
3°	9860.1
3.5°	9739.7
4°	9560.9
4.5°	9343.4
5°	9069.4
5.5°	8709.0
6°	8339.7
6.5°	7916.5
7°	7502.2
7.5°	7017.0
8°	6583.9
8.5°	6148.1
9°	5745.5
9.5°	5376.2
10°	5032.0
12.5°	3613.2
15°	2508.8
17.5°	1639.0
20°	1033.4
22.5°	669.4
25°	460.1
27.5°	323.5
30°	232.7
32.5°	167.1
35°	118.6
37.5°	82.7
40°	59.3
42.5°	43.1
45°	32.3
47.5°	25.2
50°	17.1
52.5°	10.8
55°	8.1
57.5°	6.3
60°	4.5
62.5°	3.6
65°	2.7



TEST NUMBER: P762005

CATALOG NUMBER: LD6D20D010-EU6DR2015309024-6LBDP1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	1.8
70°	0.9



(END OF REPORT)