

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770811

Luminaire Tested: LD6D70BD010-EU6DR6070959050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6070959050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9531.2 lumens
Efficiency: N/A
Efficacy: 143.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P770811

CATALOG NUMBER: LD6D70BD010-EU6DR6070959050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P770811

CATALOG NUMBER: LD6D70BD010-EU6DR6070959050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106	111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96	106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87	100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80	95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74	91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68	86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63	82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59	78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55	74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52	71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1042151
5°	1039606
10°	1074137
15°	1075238
20°	989343
25°	841504
30°	641201
35°	453421
40°	266261
45°	107436
50°	35866
55°	17258
60°	7102
65°	1060
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 107436 cd/sqm



TEST NUMBER: P770811

CATALOG NUMBER: LD6D70BD010-EU6DR6070959050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	914.4	9.6
10°-20°	2633.4	27.6
20°-30°	3151.9	33.1
30°-40°	2108.1	22.1
40°-50°	625.0	6.6
50°-60°	89.9	0.9
60°-70°	8.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6699.7	70.3
0°-40°	8807.8	92.4
0°-60°	9522.6	99.9
0°-90°	9531.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9531.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9538	
5°	9479	914
15°	9506	2633
25°	6980	3152
35°	3399	2108
45°	695	625
55°	91	90
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P770811

CATALOG NUMBER: LD6D70BD010-EU6DR6070959050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9538.2
2.5°	9526.0
5°	9478.7
7.5°	9607.2
10°	9681.6
12.5°	9668.1
15°	9505.7
17.5°	9122.9
20°	8508.8
22.5°	7771.5
25°	6980.2
27.5°	6088.7
30°	5082.3
32.5°	4184.0
35°	3399.4
37.5°	2613.5
40°	1866.8
42.5°	1231.0
45°	695.3
47.5°	355.8
50°	211.0
52.5°	136.6
55°	90.6
57.5°	58.2
60°	32.5
62.5°	13.5
65°	4.1
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)