

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770992

Luminaire Tested: LD6D75BD010-EU6DR2570959027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR2570959027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7788.6 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P770992

CATALOG NUMBER: LD6D75BD010-EU6DR2570959027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P770992

CATALOG NUMBER: LD6D75BD010-EU6DR2570959027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3227595
5°	3006102
10°	2144336
15°	1262930
20°	785819
25°	431253
30°	197231
35°	74694
40°	33832
45°	20335
50°	8448
55°	5448
60°	3802
65°	2559
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20335 cd/sqm



TEST NUMBER: P770992

CATALOG NUMBER: LD6D75BD010-EU6DR2570959027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2355.5	30.2
10°-20°	3190.4	41.0
20°-30°	1688.3	21.7
30°-40°	416.8	5.4
40°-50°	101.7	1.3
50°-60°	26.8	0.3
60°-70°	9.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7234.2	92.9
0°-40°	7651.0	98.2
0°-60°	7779.5	99.9
0°-90°	7788.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7788.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	29540	
5°	27408	###
15°	11165	3190
25°	3577	1688
35°	560	417
45°	132	102
55°	29	27
65°	10	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P770992

CATALOG NUMBER: LD6D75BD010-EU6DR2570959027-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	29540.3
2.5°	29054.9
5°	27408.4
7.5°	24100.6
10°	19327.7
12.5°	14610.6
15°	11165.0
17.5°	8701.6
20°	6758.4
22.5°	5068.5
25°	3577.2
27.5°	2398.9
30°	1563.3
32.5°	951.1
35°	560.0
37.5°	342.7
40°	237.2
42.5°	181.3
45°	131.6
47.5°	79.5
50°	49.7
52.5°	36.0
55°	28.6
57.5°	22.3
60°	17.4
62.5°	13.7
65°	9.9
67.5°	3.7
70°	1.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)