

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771640

Luminaire Tested: LD6D75BD010-EU6DR6570959035-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959035-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6517.7 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P771640

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P771640

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	701148
5°	701721
10°	726432
15°	727635
20°	669906
25°	570796
30°	436967
35°	308701
40°	182224
45°	73983
50°	26823
55°	14934
60°	8566
65°	4705
70°	4952
75°	3842
80°	4027
85°	3385

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 73983 cd/sqm



TEST NUMBER: P771640

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	617.9	9.5
10°-20°	1782.4	27.3
20°-30°	2138.6	32.8
30°-40°	1437.2	22.1
40°-50°	430.2	6.6
50°-60°	75.9	1.2
60°-70°	21.6	0.3
70°-80°	10.6	0.2
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4538.9	69.6
0°-40°	5976.1	91.7
0°-60°	6482.2	99.5
0°-90°	6517.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6517.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6417	
5°	6398	618
15°	6433	1782
25°	4735	2139
35°	2314	1437
45°	479	430
55°	78	76
65°	18	22
75°	9	11
85°	3	3
90°	0	



TEST NUMBER: P771640

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6417.2
2.5°	6444.5
5°	6398.0
7.5°	6494.7
10°	6547.6
12.5°	6534.8
15°	6432.7
17.5°	6182.8
20°	5761.5
22.5°	5265.4
25°	4734.7
27.5°	4135.5
30°	3463.5
32.5°	2854.3
35°	2314.4
37.5°	1781.0
40°	1277.6
42.5°	834.4
45°	478.8
47.5°	253.5
50°	157.8
52.5°	109.4
55°	78.4
57.5°	56.5
60°	39.2
62.5°	25.5
65°	18.2
67.5°	16.4
70°	15.5
72.5°	11.9
75°	9.1
77.5°	8.2
80°	6.4
82.5°	4.6
85°	2.7
87.5°	1.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)