

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771344

Luminaire Tested: LD6D75BD010-EU6DR4570959040-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR4570959040-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10215.5 lumens
Efficiency: N/A
Efficacy: 141.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P771344

CATALOG NUMBER: LD6D75BD010-EU6DR4570959040-6LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P771344

CATALOG NUMBER: LD6D75BD010-EU6DR4570959040-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1972834
5°	1916658
10°	1833720
15°	1678243
20°	1331429
25°	831233
30°	458150
35°	205716
40°	81028
45°	38181
50°	18103
55°	9467
60°	4655
65°	1112
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38181 cd/sqm



TEST NUMBER: P771344

CATALOG NUMBER: LD6D75BD010-EU6DR4570959040-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1642.0	16.1
10°-20°	4041.1	39.6
20°-30°	3200.1	31.3
30°-40°	1065.7	10.4
40°-50°	211.5	2.1
50°-60°	48.0	0.5
60°-70°	6.9	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8883.2	87.0
0°-40°	9948.9	97.4
0°-60°	10208.4	99.9
0°-90°	10215.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10215.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18056	
5°	17475	###
15°	14837	4041
25°	6895	3200
35°	1542	1066
45°	247	212
55°	50	48
65°	4	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P771344

CATALOG NUMBER: LD6D75BD010-EU6DR4570959040-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	18056.2
2.5°	17938.3
5°	17475.3
7.5°	17093.3
10°	16528.0
12.5°	15775.3
15°	14836.6
17.5°	13424.9
20°	11450.9
22.5°	9099.1
25°	6895.0
27.5°	5048.7
30°	3631.4
32.5°	2469.7
35°	1542.3
37.5°	914.6
40°	568.1
42.5°	373.5
45°	247.1
47.5°	159.1
50°	106.5
52.5°	71.0
55°	49.7
57.5°	32.7
60°	21.3
62.5°	11.4
65°	4.3
67.5°	1.4
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)