

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771910

Luminaire Tested: LD6D80BD010-EU6DR3570959024-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR3570959024-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6847.4 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P771910

CATALOG NUMBER: LD6D80BD010-EU6DR3570959024-6LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P771910

CATALOG NUMBER: LD6D80BD010-EU6DR3570959024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2058516
5°	2010148
10°	1811675
15°	1406156
20°	797550
25°	310287
30°	115755
35°	63450
40°	41477
45°	25248
50°	16063
55°	11353
60°	8304
65°	4524
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25248 cd/sqm



TEST NUMBER: P771910

CATALOG NUMBER: LD6D80BD010-EU6DR3570959024-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1685.6	24.6
10°-20°	3291.1	48.1
20°-30°	1342.2	19.6
30°-40°	321.2	4.7
40°-50°	133.9	2.0
50°-60°	55.4	0.8
60°-70°	17.3	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6318.9	92.3
0°-40°	6640.1	97.0
0°-60°	6829.4	99.7
0°-90°	6847.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6847.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18840	
5°	18328	###
15°	12431	3291
25°	2574	1342
35°	476	321
45°	163	134
55°	60	55
65°	18	17
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P771910

CATALOG NUMBER: LD6D80BD010-EU6DR3570959024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	18840.4
2.5°	18727.4
5°	18327.7
7.5°	17530.4
10°	16329.3
12.5°	14638.2
15°	12431.2
17.5°	9732.1
20°	6859.3
22.5°	4373.9
25°	2573.8
27.5°	1454.9
30°	917.5
32.5°	644.2
35°	475.7
37.5°	367.8
40°	290.8
42.5°	224.0
45°	163.4
47.5°	122.3
50°	94.5
52.5°	75.0
55°	59.6
57.5°	48.3
60°	38.0
62.5°	27.7
65°	17.5
67.5°	6.2
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)