

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761993

Luminaire Tested: LD6D20D010-EU6DR1515309050-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P761993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR1515309050-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2180.2 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P761993

CATALOG NUMBER: LD6D20D010-EU6DR1515309050-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P761993

CATALOG NUMBER: LD6D20D010-EU6DR1515309050-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101
2	113	110	107	105	111	108	106	104	105	103	102		102	101	100		100
3	110	106	103	101	108	105	102	100	103	100	99		100	99	97		98
4	108	103	100	98	106	102	99	97	100	98	96		99	97	95		97
5	106	101	98	95	104	100	97	95	98	96	94		97	95	93		96
6	104	99	95	93	102	98	95	93	97	94	92		96	93	92		95
7	102	97	94	91	101	96	93	91	95	93	91		94	92	90		93
8	100	95	92	90	99	95	92	90	94	91	89		93	91	89		92
9	99	93	90	88	98	93	90	88	92	90	88		92	89	88		91
10	97	92	89	87	96	92	89	87	91	89	87		91	88	87		90

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3342394	3342394	3342394
5°	1964151	1938714	1954049
10°	586205	590310	599352
15°	145815	148655	144069
20°	43628	50517	44553
25°	15378	19592	15572
30°	5654	7436	5743
35°	2832	3195	2738
40°	1790	1967	1790
45°	1323	1407	1323
50°	1050	1050	1050
55°	877	877	877
60°	709	709	709
65°	535	535	535
70°	461	461	461
75°	287	287	378
80°	197	197	197
85°	108	108	108

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 1407 cd/sqm



TEST NUMBER: P761993

CATALOG NUMBER: LD6D20D010-EU6DR1515309050-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1414.0	64.9
10°-20°	581.6	26.7
20°-30°	115.5	5.3
30°-40°	28.8	1.3
40°-50°	15.2	0.7
50°-60°	11.2	0.5
60°-70°	7.9	0.4
70°-80°	4.5	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2111.2	96.8
0°-40°	2140.0	98.2
0°-60°	2166.4	99.4
0°-90°	2180.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2180.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	29705	29705	29705	29705	29705	
5°	19327	19128	19076	19208	19227	1411
15°	1679	1710	1712	1681	1659	576
25°	197	224	252	223	200	104
35°	39	42	44	42	38	26
45°	19	19	20	19	19	15
55°	13	13	13	13	13	11
65°	8	8	8	8	8	8
75°	4	4	4	4	5	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P761993

CATALOG NUMBER: LD6D20D010-EU6DR1515309050-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	29704.9	29704.9	29704.9	29704.9	29704.9
2.5°	26795.0	26817.6	26826.4	26852.8	26950.9
5°	19326.7	19128.0	19076.4	19208.4	19227.3
7.5°	11448.4	11488.6	11635.7	11668.4	11550.2
10°	6282.5	6334.1	6326.5	6371.8	6423.4
12.5°	3212.9	3172.7	3160.1	3211.7	3140.0
15°	1678.8	1710.2	1711.5	1681.3	1658.7
17.5°	902.9	939.4	999.7	950.7	875.2
20°	533.2	565.9	617.4	577.2	544.5
22.5°	329.5	355.9	392.3	360.9	334.5
25°	197.4	223.8	251.5	222.6	199.9
27.5°	116.9	139.6	157.2	138.3	115.7
30°	75.5	88.0	99.3	86.8	76.7
32.5°	52.8	57.8	62.9	57.8	52.8
35°	39.0	41.5	44.0	41.5	37.7
37.5°	30.2	32.7	34.0	31.4	28.9
40°	25.2	26.4	27.7	26.4	25.2
42.5°	21.4	22.6	22.6	22.6	21.4
45°	18.9	18.9	20.1	18.9	18.9
47.5°	16.3	16.3	17.6	16.3	16.3
50°	15.1	15.1	15.1	15.1	15.1
52.5°	13.8	13.8	13.8	13.8	13.8
55°	12.6	12.6	12.6	12.6	12.6
57.5°	11.3	11.3	11.3	11.3	11.3
60°	10.1	10.1	10.1	10.1	10.1
62.5°	8.8	8.8	8.8	8.8	8.8
65°	7.5	7.5	7.5	7.5	7.5
67.5°	7.5	7.5	7.5	7.5	7.5
70°	6.3	6.3	6.3	6.3	6.3
72.5°	5.0	5.0	5.0	5.0	5.0
75°	3.8	3.8	3.8	3.8	5.0
77.5°	3.8	3.8	3.8	3.8	3.8
80°	2.5	2.5	2.5	2.5	2.5
82.5°	2.5	2.5	2.5	2.5	2.5
85°	1.3	1.3	1.3	1.3	1.3
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)