

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762073

Luminaire Tested: LD6D20D010-EU6DR2015309050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR2015309050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2146.1 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762073

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P762073

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1334565
5°	1204024
10°	675763
15°	343508
20°	145434
25°	67138
30°	35540
35°	19154
40°	10241
45°	6057
50°	3519
55°	1867
60°	1180
65°	853
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6057 cd/sqm



TEST NUMBER: P762073

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	869.6	40.5
10°-20°	856.3	39.9
20°-30°	279.8	13.0
30°-40°	95.3	4.4
40°-50°	32.0	1.5
50°-60°	9.7	0.4
60°-70°	3.2	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2005.7	93.5
0°-40°	2101.0	97.9
0°-60°	2142.7	99.8
0°-90°	2146.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2146.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12214	
5°	10978	870
15°	3037	856
25°	557	280
35°	144	95
45°	39	32
55°	10	10
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762073

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	12214.5
0.5°	12214.5
1°	12199.2
1.5°	12168.8
2°	12113.3
2.5°	12039.3
3°	11934.9
3.5°	11789.2
4°	11572.7
4.5°	11309.5
5°	10977.8
5.5°	10541.6
6°	10094.6
6.5°	9582.3
7°	9080.9
7.5°	8493.6
8°	7969.3
8.5°	7441.8
9°	6954.5
9.5°	6507.5
10°	6090.9
12.5°	4373.5
15°	3036.8
17.5°	1983.9
20°	1250.8
22.5°	810.3
25°	556.9
27.5°	391.6
30°	281.7
32.5°	202.3
35°	143.6
37.5°	100.1
40°	71.8
42.5°	52.2
45°	39.2
47.5°	30.5
50°	20.7
52.5°	13.1
55°	9.8
57.5°	7.6
60°	5.4
62.5°	4.4
65°	3.3



TEST NUMBER: P762073

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	2.2
70°	1.1



(END OF REPORT)