

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772020

Luminaire Tested: LD6D80BD010-EU6DR4070959030-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772020
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR4070959030-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11152.1 lumens
Efficiency: N/A
Efficacy: 141.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P772020

CATALOG NUMBER: LD6D80BD010-EU6DR4070959030-6LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P772020

CATALOG NUMBER: LD6D80BD010-EU6DR4070959030-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2836955
5°	2823169
10°	2668513
15°	2268568
20°	1546197
25°	645143
30°	202846
35°	94275
40°	52145
45°	23904
50°	11610
55°	6362
60°	3322
65°	1189
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23904 cd/sqm



TEST NUMBER: P772020

CATALOG NUMBER: LD6D80BD010-EU6DR4070959030-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2403.5	21.6
10°-20°	5384.5	48.3
20°-30°	2695.3	24.2
30°-40°	494.1	4.4
40°-50°	136.3	1.2
50°-60°	32.0	0.3
60°-70°	6.1	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10483.3	94.0
0°-40°	10977.4	98.4
0°-60°	11145.8	99.9
0°-90°	11152.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11152.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25965	
5°	25740	###
15°	20055	5385
25°	5351	2695
35°	707	494
45°	155	136
55°	33	32
65°	5	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772020

CATALOG NUMBER: LD6D80BD010-EU6DR4070959030-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	25965.0
2.5°	25927.1
5°	25740.5
7.5°	25145.9
10°	24052.3
12.5°	22347.4
15°	20055.4
17.5°	17074.9
20°	13298.0
22.5°	9066.1
25°	5351.4
27.5°	2828.9
30°	1607.8
32.5°	1039.0
35°	706.8
37.5°	505.1
40°	365.6
42.5°	250.3
45°	154.7
47.5°	98.6
50°	68.3
52.5°	48.5
55°	33.4
57.5°	21.2
60°	15.2
62.5°	9.1
65°	4.6
67.5°	3.0
70°	1.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)