

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762075

Luminaire Tested: LD6D20D010-EU6DR2015309050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D20D010-EU6DR2015309050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2407.9 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762075

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P762075

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		113	111	109	108		107	106	104		103	102	101		100	99	98
2	111	108	105	102		109	106	104	101		103	101	99		100	99	97		98	96	95
3	108	103	100	97		106	102	99	96		100	97	95		97	95	93		95	93	92
4	105	99	96	93		103	98	95	92		96	93	91		95	92	90		93	91	89
5	102	96	92	89		100	95	91	89		94	90	88		92	89	87		91	88	86
6	99	93	89	86		98	92	88	86		91	87	85		90	87	84		88	86	84
7	96	90	86	83		95	89	86	83		88	85	82		87	84	82		86	84	82
8	94	87	83	81		93	87	83	80		86	83	80		85	82	80		84	82	80
9	91	85	81	78		91	85	81	78		84	80	78		83	80	78		82	80	78
10	89	83	79	76		88	82	79	76		82	78	76		81	78	76		81	78	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1497473
5°	1350993
10°	758251
15°	385428
20°	163189
25°	75335
30°	39880
35°	21488
40°	11482
45°	6783
50°	3944
55°	2095
60°	1333
65°	957
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6783 cd/sqm



TEST NUMBER: P762075

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	975.8	40.5
10°-20°	960.9	39.9
20°-30°	313.9	13.0
30°-40°	106.9	4.4
40°-50°	35.9	1.5
50°-60°	10.8	0.4
60°-70°	3.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2250.6	93.5
0°-40°	2357.4	97.9
0°-60°	2404.2	99.8
0°-90°	2407.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2407.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13706	
5°	12318	976
15°	3407	961
25°	625	314
35°	161	107
45°	44	36
55°	11	11
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762075

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13705.5
0.5°	13705.5
1°	13688.4
1.5°	13654.2
2°	13592.0
2.5°	13509.0
3°	13391.8
3.5°	13228.3
4°	12985.4
4.5°	12690.1
5°	12317.8
5.5°	11828.4
6°	11326.8
6.5°	10752.0
7°	10189.4
7.5°	9530.4
8°	8942.1
8.5°	8350.2
9°	7803.4
9.5°	7301.8
10°	6834.4
12.5°	4907.4
15°	3407.4
17.5°	2226.1
20°	1403.5
22.5°	909.2
25°	624.9
27.5°	439.4
30°	316.1
32.5°	227.0
35°	161.1
37.5°	112.3
40°	80.5
42.5°	58.6
45°	43.9
47.5°	34.2
50°	23.2
52.5°	14.6
55°	11.0
57.5°	8.5
60°	6.1
62.5°	4.9
65°	3.7



TEST NUMBER: P762075

CATALOG NUMBER: LD6D20D010-EU6DR2015309050-6LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	2.4
70°	1.2



(END OF REPORT)