

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762995

Luminaire Tested: LD6D25D010-EU6DR2015309040-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR2015309040-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3004.2 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762995

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P762995

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	87	85		90	87	84		88
7	96	90	86	83	95	89	86	83	88	85	82		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1868293
5°	1685544
10°	946028
15°	480875
20°	203605
25°	93985
30°	49759
35°	26810
40°	14334
45°	8468
50°	4912
55°	2610
60°	1661
65°	1189
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8468 cd/sqm



TEST NUMBER: P762995

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1217.4	40.5
10°-20°	1198.8	39.9
20°-30°	391.6	13.0
30°-40°	133.3	4.4
40°-50°	44.8	1.5
50°-60°	13.5	0.4
60°-70°	4.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2807.9	93.5
0°-40°	2941.2	97.9
0°-60°	2999.6	99.8
0°-90°	3004.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3004.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17099	
5°	15368	###
15°	4251	1199
25°	780	392
35°	201	133
45°	55	45
55°	14	14
65°	5	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762995

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	17099.4
0.5°	17099.4
1°	17078.1
1.5°	17035.4
2°	16957.8
2.5°	16854.2
3°	16708.1
3.5°	16504.0
4°	16201.0
4.5°	15832.5
5°	15368.1
5.5°	14757.6
6°	14131.7
6.5°	13414.6
7°	12712.6
7.5°	11890.4
8°	11156.5
8.5°	10418.0
9°	9735.8
9.5°	9110.0
10°	8526.9
12.5°	6122.6
15°	4251.2
17.5°	2777.3
20°	1751.1
22.5°	1134.4
25°	779.6
27.5°	548.2
30°	394.4
32.5°	283.2
35°	201.0
37.5°	140.1
40°	100.5
42.5°	73.1
45°	54.8
47.5°	42.6
50°	28.9
52.5°	18.3
55°	13.7
57.5°	10.7
60°	7.6
62.5°	6.1
65°	4.6



TEST NUMBER: P762995

CATALOG NUMBER: LD6D25D010-EU6DR2015309040-6LBDP1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	3.0
70°	1.5



(END OF REPORT)