

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763880

Luminaire Tested: LD6D30D010-EU6DR2015309024-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763880
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D30D010-EU6DR2015309024-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2902.3 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763880

CATALOG NUMBER: LD6D30D010-EU6DR2015309024-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P763880

CATALOG NUMBER: LD6D30D010-EU6DR2015309024-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		113	111	109	108		107	106	104		103	102	101		100	99	98
2	111	108	105	102		109	106	104	101		103	101	99		100	99	97		98	96	95
3	108	103	100	97		106	102	99	96		100	97	95		97	95	93		95	93	92
4	105	99	96	93		103	98	95	92		96	93	91		95	92	90		93	91	89
5	102	96	92	89		100	95	91	89		94	90	88		92	89	87		91	88	86
6	99	93	89	86		98	92	88	86		91	87	85		90	87	84		88	86	84
7	96	90	86	83		95	89	86	83		88	85	82		87	84	82		86	84	82
8	94	87	83	81		93	87	83	80		86	83	80		85	82	80		84	82	80
9	91	85	81	78		91	85	81	78		84	80	78		83	80	78		82	80	78
10	89	83	79	76		88	82	79	76		82	78	76		81	78	76		81	78	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1804878
5°	1628336
10°	913909
15°	464552
20°	196687
25°	90791
30°	48068
35°	25903
40°	13849
45°	8189
50°	4742
55°	2514
60°	1617
65°	1138
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8189 cd/sqm



TEST NUMBER: P763880

CATALOG NUMBER: LD6D30D010-EU6DR2015309024-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1176.1	40.5
10°-20°	1158.1	39.9
20°-30°	378.3	13.0
30°-40°	128.8	4.4
40°-50°	43.3	1.5
50°-60°	13.0	0.4
60°-70°	4.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2712.6	93.5
0°-40°	2841.4	97.9
0°-60°	2897.7	99.8
0°-90°	2902.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2902.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16519	
5°	14846	###
15°	4107	1158
25°	753	378
35°	194	129
45°	53	43
55°	13	13
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P763880

CATALOG NUMBER: LD6D30D010-EU6DR2015309024-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	16519.0
0.5°	16519.0
1°	16498.4
1.5°	16457.2
2°	16382.2
2.5°	16282.2
3°	16140.9
3.5°	15943.8
4°	15651.1
4.5°	15295.1
5°	14846.5
5.5°	14256.6
6°	13652.1
6.5°	12959.2
7°	12281.1
7.5°	11486.8
8°	10777.8
8.5°	10064.4
9°	9405.4
9.5°	8800.8
10°	8237.4
12.5°	5914.8
15°	4106.9
17.5°	2683.0
20°	1691.6
22.5°	1095.9
25°	753.1
27.5°	529.5
30°	381.0
32.5°	273.6
35°	194.2
37.5°	135.3
40°	97.1
42.5°	70.6
45°	53.0
47.5°	41.2
50°	27.9
52.5°	17.7
55°	13.2
57.5°	10.3
60°	7.4
62.5°	5.9
65°	4.4



TEST NUMBER: P763880

CATALOG NUMBER: LD6D30D010-EU6DR2015309024-6LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	2.9
70°	1.5



(END OF REPORT)