

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772718

Luminaire Tested: LD6D85BD010-EU6DR3570959030-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR3570959030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10319.4 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P772718

CATALOG NUMBER: LD6D85BD010-EU6DR3570959030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P772718

CATALOG NUMBER: LD6D85BD010-EU6DR3570959030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3102339
5°	3029441
10°	2730332
15°	2119177
20°	1201959
25°	467624
30°	174459
35°	95622
40°	62500
45°	38042
50°	24222
55°	17106
60°	12521
65°	6799
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38042 cd/sqm



TEST NUMBER: P772718

CATALOG NUMBER: LD6D85BD010-EU6DR3570959030-6LBPD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2540.3	24.6
10°-20°	4959.8	48.1
20°-30°	2022.8	19.6
30°-40°	484.1	4.7
40°-50°	201.7	2.0
50°-60°	83.5	0.8
60°-70°	26.1	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9523.0	92.3
0°-40°	10007.0	97.0
0°-60°	10292.3	99.7
0°-90°	10319.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10319.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	28394	
5°	27621	###
15°	18735	4960
25°	3879	2023
35°	717	484
45°	246	202
55°	90	84
65°	26	26
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P772718

CATALOG NUMBER: LD6D85BD010-EU6DR3570959030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	28393.9
2.5°	28223.6
5°	27621.2
7.5°	26419.6
10°	24609.5
12.5°	22060.7
15°	18734.7
17.5°	14666.9
20°	10337.4
22.5°	6591.7
25°	3878.9
27.5°	2192.6
30°	1382.8
32.5°	970.9
35°	716.9
37.5°	554.3
40°	438.2
42.5°	337.6
45°	246.2
47.5°	184.3
50°	142.5
52.5°	113.0
55°	89.8
57.5°	72.8
60°	57.3
62.5°	41.8
65°	26.3
67.5°	9.3
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)