

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774256

Luminaire Tested: LD6D95BD010-EU6DR3570959024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10114.1 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774256

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774256

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3040596
5°	2969151
10°	2675991
15°	2076996
20°	1178042
25°	458317
30°	170977
35°	93728
40°	61259
45°	37285
50°	23729
55°	16763
60°	12281
65°	6670
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37285 cd/sqm



TEST NUMBER: P774256

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2489.8	24.6
10°-20°	4861.1	48.1
20°-30°	1982.6	19.6
30°-40°	474.5	4.7
40°-50°	197.7	2.0
50°-60°	81.8	0.8
60°-70°	25.6	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9333.5	92.3
0°-40°	9807.9	97.0
0°-60°	10087.5	99.7
0°-90°	10114.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10114.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27829	
5°	27072	###
15°	18362	4861
25°	3802	1983
35°	703	474
45°	241	198
55°	88	82
65°	26	26
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774256

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	27828.8
2.5°	27661.9
5°	27071.5
7.5°	25893.8
10°	24119.7
12.5°	21621.7
15°	18361.8
17.5°	14375.0
20°	10131.7
22.5°	6460.6
25°	3801.7
27.5°	2149.0
30°	1355.2
32.5°	951.6
35°	702.7
37.5°	543.3
40°	429.5
42.5°	330.8
45°	241.3
47.5°	180.6
50°	139.6
52.5°	110.8
55°	88.0
57.5°	71.3
60°	56.2
62.5°	41.0
65°	25.8
67.5°	9.1
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)