

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774257

Luminaire Tested: LD6D95BD010-EU6DR3570959024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9156.6 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774257

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P774257

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2752748
5°	2688068
10°	2422667
15°	1880379
20°	1066524
25°	414929
30°	154790
35°	84845
40°	55454
45°	33762
50°	21485
55°	15182
60°	11101
65°	6050
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33762 cd/sqm



TEST NUMBER: P774257

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2254.1	24.6
10°-20°	4400.9	48.1
20°-30°	1794.9	19.6
30°-40°	429.5	4.7
40°-50°	179.0	2.0
50°-60°	74.1	0.8
60°-70°	23.2	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8449.9	92.3
0°-40°	8879.4	97.0
0°-60°	9132.5	99.7
0°-90°	9156.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9156.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25194	
5°	24509	###
15°	16624	4401
25°	3442	1795
35°	636	430
45°	218	179
55°	80	74
65°	23	23
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774257

CATALOG NUMBER: LD6D95BD010-EU6DR3570959024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	25194.3
2.5°	25043.2
5°	24508.7
7.5°	23442.5
10°	21836.4
12.5°	19574.8
15°	16623.6
17.5°	13014.2
20°	9172.6
22.5°	5849.0
25°	3441.8
27.5°	1945.5
30°	1226.9
32.5°	861.5
35°	636.1
37.5°	491.9
40°	388.8
42.5°	299.5
45°	218.5
47.5°	163.5
50°	126.4
52.5°	100.3
55°	79.7
57.5°	64.6
60°	50.8
62.5°	37.1
65°	23.4
67.5°	8.2
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)