

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774563

Luminaire Tested: LD6D95BD010-EU6DR5570959024-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5570959024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9796.6 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774563

CATALOG NUMBER: LD6D95BD010-EU6DR5570959024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P774563

CATALOG NUMBER: LD6D95BD010-EU6DR5570959024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1200262
5°	1152596
10°	1148250
15°	1115269
20°	999993
25°	826447
30°	624282
35°	452648
40°	289681
45°	132298
50°	43277
55°	18668
60°	8042
65°	1060
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 132298 cd/sqm



TEST NUMBER: P774563

CATALOG NUMBER: LD6D95BD010-EU6DR5570959024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1000.0	10.2
10°-20°	2729.1	27.9
20°-30°	3110.1	31.7
30°-40°	2117.2	21.6
40°-50°	729.6	7.4
50°-60°	100.9	1.0
60°-70°	9.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6839.2	69.8
0°-40°	8956.4	91.4
0°-60°	9786.9	99.9
0°-90°	9796.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9796.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10985	
5°	10509	###
15°	9860	2729
25°	6855	3110
35°	3394	2117
45°	856	730
55°	98	101
65°	4	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774563

CATALOG NUMBER: LD6D95BD010-EU6DR5570959024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	10985.3
2.5°	10733.5
5°	10508.9
7.5°	10398.6
10°	10349.6
12.5°	10186.3
15°	9859.6
17.5°	9340.9
20°	8600.4
22.5°	7745.6
25°	6855.3
27.5°	5928.3
30°	4948.2
32.5°	4117.8
35°	3393.6
37.5°	2704.8
40°	2031.0
42.5°	1407.5
45°	856.2
47.5°	461.5
50°	254.6
52.5°	151.1
55°	98.0
57.5°	62.6
60°	36.8
62.5°	16.3
65°	4.1
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)