

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774640

Luminaire Tested: LD6D95BD010-EU6DR6070959024-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959024-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7565.7 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774640

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P774640

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	981741
5°	1005880
10°	1018032
15°	969815
20°	855071
25°	691605
30°	467814
35°	234420
40°	38025
45°	37223
50°	37956
55°	38536
60°	39596
65°	40512
70°	41466
75°	41962
80°	40458
85°	33723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 41962 cd/sqm



TEST NUMBER: P774640

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBPD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	876.5	11.6
10°-20°	2371.5	31.3
20°-30°	2551.6	33.7
30°-40°	1109.1	14.7
40°-50°	186.3	2.5
50°-60°	181.1	2.4
60°-70°	154.9	2.0
70°-80°	103.7	1.4
80°-90°	31.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5799.6	76.7
0°-40°	6908.7	91.3
0°-60°	7276.1	96.2
0°-90°	7565.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7565.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8985	
5°	9171	877
15°	8574	2372
25°	5737	2552
35°	1758	1109
45°	241	186
55°	202	181
65°	157	155
75°	99	104
85°	27	31
90°	0	



TEST NUMBER: P774640

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8985.3
2.5°	9237.9
5°	9171.2
7.5°	9192.2
10°	9175.9
12.5°	8986.4
15°	8573.7
17.5°	8019.4
20°	7354.0
22.5°	6641.9
25°	5736.8
27.5°	4588.5
30°	3708.0
32.5°	2857.9
35°	1757.5
37.5°	751.9
40°	266.6
42.5°	245.6
45°	240.9
47.5°	232.7
50°	223.3
52.5°	212.8
55°	202.3
57.5°	191.8
60°	181.2
62.5°	169.6
65°	156.7
67.5°	143.8
70°	129.8
72.5°	114.6
75°	99.4
77.5°	81.9
80°	64.3
82.5°	45.6
85°	26.9
87.5°	9.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)