

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774647

Luminaire Tested: LD6D95BD010-EU6DR6070959024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9611.2 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774647

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774647

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63		82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1050892
5°	1048325
10°	1083146
15°	1084264
20°	997644
25°	848557
30°	646575
35°	457236
40°	268501
45°	108333
50°	36172
55°	17411
60°	7146
65°	1060
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 108333 cd/sqm



TEST NUMBER: P774647

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	922.0	9.6
10°-20°	2655.5	27.6
20°-30°	3178.3	33.1
30°-40°	2125.8	22.1
40°-50°	630.3	6.6
50°-60°	90.6	0.9
60°-70°	8.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6755.9	70.3
0°-40°	8881.7	92.4
0°-60°	9602.6	99.9
0°-90°	9611.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9611.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9618	
5°	9558	922
15°	9586	2656
25°	7039	3178
35°	3428	2126
45°	701	630
55°	91	91
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774647

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9618.2
2.5°	9606.0
5°	9558.2
7.5°	9687.8
10°	9762.8
12.5°	9749.2
15°	9585.5
17.5°	9199.5
20°	8580.2
22.5°	7836.7
25°	7038.7
27.5°	6139.8
30°	5124.9
32.5°	4219.1
35°	3428.0
37.5°	2635.4
40°	1882.5
42.5°	1241.3
45°	701.1
47.5°	358.8
50°	212.8
52.5°	137.8
55°	91.4
57.5°	58.7
60°	32.7
62.5°	13.6
65°	4.1
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)