

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768075

Luminaire Tested: LD6D55D010-EU6DR3555659050-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR3555659050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5734.8 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P768075

CATALOG NUMBER: LD6D55D010-EU6DR3555659050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P768075

CATALOG NUMBER: LD6D55D010-EU6DR3555659050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96						
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88						
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84						
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81						
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78						
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75						
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72						
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70						
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1724069
5°	1683559
10°	1517335
15°	1177697
20°	667964
25°	259870
30°	96944
35°	53140
40°	34730
45°	21138
50°	13462
55°	9505
60°	6949
65°	3775
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21138 cd/sqm

TEST NUMBER: P768075

CATALOG NUMBER: LD6D55D010-EU6DR3555659050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1411.7	24.6
10°-20°	2756.3	48.1
20°-30°	1124.1	19.6
30°-40°	269.0	4.7
40°-50°	112.1	2.0
50°-60°	46.4	0.8
60°-70°	14.5	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5292.2	92.3
0°-40°	5561.2	97.0
0°-60°	5719.7	99.7
0°-90°	5734.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5734.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15779	
5°	15350	###
15°	10412	2756
25°	2156	1124
35°	398	269
45°	137	112
55°	50	46
65°	15	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768075

CATALOG NUMBER: LD6D55D010-EU6DR3555659050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	15779.4
2.5°	15684.7
5°	15350.0
7.5°	14682.2
10°	13676.3
12.5°	12259.9
15°	10411.5
17.5°	8150.9
20°	5744.8
22.5°	3663.2
25°	2155.6
27.5°	1218.5
30°	768.4
32.5°	539.5
35°	398.4
37.5°	308.1
40°	243.5
42.5°	187.6
45°	136.8
47.5°	102.4
50°	79.2
52.5°	62.8
55°	49.9
57.5°	40.4
60°	31.8
62.5°	23.2
65°	14.6
67.5°	5.2
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)