

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774800

Luminaire Tested: LD6D95BD010-EU6DR7070959024-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR7070959024-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9475.3 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774800

CATALOG NUMBER: LD6D95BD010-EU6DR7070959024-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P774800

CATALOG NUMBER: LD6D95BD010-EU6DR7070959024-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	817139
5°	815095
10°	813325
15°	813105
20°	805155
25°	756344
30°	674281
35°	537599
40°	356974
45°	213420
50°	110640
55°	58157
60°	20563
65°	336
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 213420 cd/sqm



TEST NUMBER: P774800

CATALOG NUMBER: LD6D95BD010-EU6DR7070959024-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	706.7	7.5
10°-20°	2027.0	21.4
20°-30°	2859.5	30.2
30°-40°	2468.5	26.1
40°-50°	1105.4	11.7
50°-60°	289.4	3.1
60°-70°	18.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5593.2	59.0
0°-40°	8061.7	85.1
0°-60°	9456.5	99.8
0°-90°	9475.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9475.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7479	
5°	7432	707
15°	7188	2027
25°	6274	2859
35°	4030	2468
45°	1381	1105
55°	305	289
65°	1	19
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774800

CATALOG NUMBER: LD6D95BD010-EU6DR7070959024-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7478.8
2.5°	7470.7
5°	7431.7
7.5°	7399.4
10°	7330.8
12.5°	7269.0
15°	7188.3
17.5°	7095.5
20°	6924.7
22.5°	6643.6
25°	6273.8
27.5°	5844.8
30°	5344.5
32.5°	4732.6
35°	4030.5
37.5°	3255.9
40°	2502.8
42.5°	1901.6
45°	1381.2
47.5°	952.2
50°	650.9
52.5°	449.2
55°	305.3
57.5°	184.2
60°	94.1
62.5°	29.6
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)