

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774265

Luminaire Tested: LD6D95BD010-EU6DR3570959027-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10884.2 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774265

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774265

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3272108
5°	3195231
10°	2879744
15°	2235142
20°	1267735
25°	493206
30°	183997
35°	100864
40°	65923
45°	40128
50°	25548
55°	18039
60°	13199
65°	7187
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40128 cd/sqm



TEST NUMBER: P774265

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBPD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2679.3	24.6
10°-20°	5231.3	48.1
20°-30°	2133.5	19.6
30°-40°	510.6	4.7
40°-50°	212.8	2.0
50°-60°	88.1	0.8
60°-70°	27.6	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10044.1	92.3
0°-40°	10554.7	97.0
0°-60°	10855.5	99.7
0°-90°	10884.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10884.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	29948	
5°	29133	###
15°	19760	5231
25°	4091	2134
35°	756	511
45°	260	213
55°	95	88
65°	28	28
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774265

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	29947.7
2.5°	29768.1
5°	29132.8
7.5°	27865.4
10°	25956.2
12.5°	23268.0
15°	19759.9
17.5°	15469.5
20°	10903.1
22.5°	6952.5
25°	4091.1
27.5°	2312.6
30°	1458.4
32.5°	1024.0
35°	756.2
37.5°	584.7
40°	462.2
42.5°	356.0
45°	259.7
47.5°	194.3
50°	150.3
52.5°	119.2
55°	94.7
57.5°	76.8
60°	60.4
62.5°	44.1
65°	27.8
67.5°	9.8
70°	1.6
72.5°	1.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)