

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774268

Luminaire Tested: LD6D95BD010-EU6DR3570959027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10911.4 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774268

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P774268

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3280314
5°	3203237
10°	2886966
15°	2240741
20°	1270921
25°	494448
30°	184464
35°	101117
40°	66080
45°	40221
50°	25599
55°	18097
60°	13242
65°	7187
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40221 cd/sqm



TEST NUMBER: P774268

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2686.1	24.6
10°-20°	5244.4	48.1
20°-30°	2138.9	19.6
30°-40°	511.8	4.7
40°-50°	213.3	2.0
50°-60°	88.3	0.8
60°-70°	27.6	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10069.3	92.3
0°-40°	10581.1	97.0
0°-60°	10882.7	99.7
0°-90°	10911.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10911.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	30023	
5°	29206	###
15°	19809	5244
25°	4101	2139
35°	758	512
45°	260	213
55°	95	88
65°	28	28
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774268

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	30022.8
2.5°	29842.7
5°	29205.8
7.5°	27935.3
10°	26021.3
12.5°	23326.3
15°	19809.4
17.5°	15508.3
20°	10930.5
22.5°	6969.9
25°	4101.4
27.5°	2318.4
30°	1462.1
32.5°	1026.6
35°	758.1
37.5°	586.1
40°	463.3
42.5°	356.9
45°	260.3
47.5°	194.8
50°	150.6
52.5°	119.5
55°	95.0
57.5°	77.0
60°	60.6
62.5°	44.2
65°	27.8
67.5°	9.8
70°	1.6
72.5°	1.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)