

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774269

Luminaire Tested: LD6D95BD010-EU6DR3570959027-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959027-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11457.0 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774269

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774269

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3444325
5°	3363400
10°	3031307
15°	2352782
20°	1334464
25°	519174
30°	193686
35°	106173
40°	69389
45°	42230
50°	26891
55°	18992
60°	13898
65°	7549
70°	543
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42230 cd/sqm



TEST NUMBER: P774269

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2820.4	24.6
10°-20°	5506.6	48.1
20°-30°	2245.8	19.6
30°-40°	537.5	4.7
40°-50°	224.0	2.0
50°-60°	92.7	0.8
60°-70°	29.0	0.3
70°-80°	0.7	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10572.8	92.3
0°-40°	11110.2	97.0
0°-60°	11426.9	99.7
0°-90°	11457.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11457.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	31524	
5°	30666	###
15°	20800	5507
25°	4306	2246
35°	796	537
45°	273	224
55°	100	93
65°	29	29
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774269

CATALOG NUMBER: LD6D95BD010-EU6DR3570959027-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	31523.9
2.5°	31334.8
5°	30666.1
7.5°	29332.0
10°	27322.3
12.5°	24492.6
15°	20799.9
17.5°	16283.7
20°	11477.0
22.5°	7318.4
25°	4306.5
27.5°	2434.3
30°	1535.2
32.5°	1077.9
35°	796.0
37.5°	615.5
40°	486.5
42.5°	374.8
45°	273.3
47.5°	204.6
50°	158.2
52.5°	125.5
55°	99.7
57.5°	80.8
60°	63.6
62.5°	46.4
65°	29.2
67.5°	10.3
70°	1.7
72.5°	1.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)