

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774343

Luminaire Tested: LD6D95BD010-EU6DR4070959027-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR4070959027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11895.8 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774343

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774343

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3026140
5°	3011443
10°	2846471
15°	2419859
20°	1649307
25°	688157
30°	216383
35°	100571
40°	55611
45°	25495
50°	12375
55°	6781
60°	3540
65°	1267
70°	511
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25495 cd/sqm

TEST NUMBER: P774343

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2563.8	21.6
10°-20°	5743.6	48.3
20°-30°	2875.1	24.2
30°-40°	527.0	4.4
40°-50°	145.4	1.2
50°-60°	34.2	0.3
60°-70°	6.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	11182.5	94.0
0°-40°	11709.5	98.4
0°-60°	11889.1	99.9
0°-90°	11895.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11895.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27696	
5°	27457	###
15°	21393	5744
25°	5708	2875
35°	754	527
45°	165	145
55°	36	34
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774343

CATALOG NUMBER: LD6D95BD010-EU6DR4070959027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	27696.5
2.5°	27656.1
5°	27457.1
7.5°	26822.8
10°	25656.3
12.5°	23837.7
15°	21392.9
17.5°	18213.6
20°	14184.8
22.5°	9670.7
25°	5708.2
27.5°	3017.5
30°	1715.1
32.5°	1108.3
35°	754.0
37.5°	538.8
40°	389.9
42.5°	267.0
45°	165.0
47.5°	105.2
50°	72.8
52.5°	51.8
55°	35.6
57.5°	22.7
60°	16.2
62.5°	9.7
65°	4.9
67.5°	3.2
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)