

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774499

Luminaire Tested: LD6D95BD010-EU6DR5070959027-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5070959027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11820.8 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774499

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P774499

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	110	108	106		106	104	102		102	101	99		98	97	97
2	109	105	101	98	107	103	100	97		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85	99	93	88	85		90	87	84		89	85	83		87	84	82
5	96	89	84	80	95	88	83	79		86	82	79		85	81	78		83	80	77
6	92	84	79	75	91	83	79	75		82	78	74		81	77	74		79	76	74
7	88	80	75	71	87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	67	84	76	71	67		75	70	67		74	70	67		73	69	66
9	81	73	68	64	80	72	67	64		71	67	64		71	67	64		70	66	63
10	78	70	64	61	77	69	64	61		68	64	61		68	64	61		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2081024
5°	2059207
10°	2025291
15°	1844194
20°	1534581
25°	1089319
30°	576580
35°	234967
40°	87261
45°	39943
50°	16369
55°	8572
60°	4217
65°	1241
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 39943 cd/sqm



TEST NUMBER: P774499

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBPD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1774.6	15.0
10°-20°	4484.8	37.9
20°-30°	4028.6	34.1
30°-40°	1261.3	10.7
40°-50°	220.8	1.9
50°-60°	44.0	0.4
60°-70°	6.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10288.0	87.0
0°-40°	11549.3	97.7
0°-60°	11814.2	99.9
0°-90°	11820.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11820.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19046	
5°	18775	###
15°	16304	4485
25°	9036	4029
35°	1762	1261
45°	258	221
55°	45	44
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774499

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	19046.4
2.5°	18951.6
5°	18775.0
7.5°	18505.2
10°	18254.7
12.5°	17451.8
15°	16303.7
17.5°	14845.6
20°	13198.1
22.5°	11292.0
25°	9035.8
27.5°	6643.2
30°	4570.1
32.5°	2975.5
35°	1761.6
37.5°	1011.7
40°	611.8
42.5°	398.2
45°	258.5
47.5°	157.4
50°	96.3
52.5°	65.8
55°	45.0
57.5°	30.5
60°	19.3
62.5°	11.2
65°	4.8
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)