

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774503

Luminaire Tested: LD6D95BD010-EU6DR5070959027-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5070959027-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12443.0 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774503

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774503

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	74	74	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	63	63	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2190547
5°	2167590
10°	2131888
15°	1941258
20°	1615344
25°	1146655
30°	606922
35°	247332
40°	91854
45°	42044
50°	17236
55°	9010
60°	4436
65°	1319
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42044 cd/sqm



TEST NUMBER: P774503

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1868.0	15.0
10°-20°	4720.9	37.9
20°-30°	4240.6	34.1
30°-40°	1327.7	10.7
40°-50°	232.5	1.9
50°-60°	46.3	0.4
60°-70°	7.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10829.5	87.0
0°-40°	12157.2	97.7
0°-60°	12436.0	99.9
0°-90°	12443.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12443.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20049	
5°	19763	###
15°	17162	4721
25°	9511	4241
35°	1854	1328
45°	272	232
55°	47	46
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774503

CATALOG NUMBER: LD6D95BD010-EU6DR5070959027-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	20048.8
2.5°	19949.1
5°	19763.2
7.5°	19479.2
10°	19215.5
12.5°	18370.3
15°	17161.8
17.5°	15627.0
20°	13892.7
22.5°	11886.3
25°	9511.4
27.5°	6992.8
30°	4810.6
32.5°	3132.2
35°	1854.3
37.5°	1064.9
40°	644.0
42.5°	419.2
45°	272.1
47.5°	165.7
50°	101.4
52.5°	69.3
55°	47.3
57.5°	32.1
60°	20.3
62.5°	11.8
65°	5.1
67.5°	1.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)