

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772238

Luminaire Tested: LD6D80BD010-EU6DR5570959027-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR5570959027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8782.4 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P772238

CATALOG NUMBER: LD6D80BD010-EU6DR5570959027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P772238

CATALOG NUMBER: LD6D80BD010-EU6DR5570959027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1076011
5°	1033277
10°	1029382
15°	999813
20°	896475
25°	740888
30°	559648
35°	405790
40°	259686
45°	118608
50°	38789
55°	16744
60°	7189
65°	957
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 118608 cd/sqm



TEST NUMBER: P772238

CATALOG NUMBER: LD6D80BD010-EU6DR5570959027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	896.5	10.2
10°-20°	2446.6	27.9
20°-30°	2788.1	31.7
30°-40°	1898.0	21.6
40°-50°	654.0	7.4
50°-60°	90.4	1.0
60°-70°	8.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6131.2	69.8
0°-40°	8029.2	91.4
0°-60°	8773.7	99.9
0°-90°	8782.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8782.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9848	
5°	9421	896
15°	8839	2447
25°	6146	2788
35°	3042	1898
45°	768	654
55°	88	90
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P772238

CATALOG NUMBER: LD6D80BD010-EU6DR5570959027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	9848.1
2.5°	9622.3
5°	9421.0
7.5°	9322.1
10°	9278.2
12.5°	9131.8
15°	8838.9
17.5°	8373.9
20°	7710.1
22.5°	6943.7
25°	6145.6
27.5°	5314.6
30°	4435.9
32.5°	3691.5
35°	3042.3
37.5°	2424.8
40°	1820.7
42.5°	1261.8
45°	767.6
47.5°	413.7
50°	228.2
52.5°	135.5
55°	87.9
57.5°	56.1
60°	32.9
62.5°	14.6
65°	3.7
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)