

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772395

Luminaire Tested: LD6D80BD010-EU6DR6570959027-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959027-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8034.4 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P772395

CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P772395

CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	426056
5°	424981
10°	424623
15°	411531
20°	374647
25°	326480
30°	271543
35°	215156
40°	155287
45°	98107
50°	51136
55°	27177
60°	14274
65°	7849
70°	3296
75°	3633
80°	2523
85°	2144

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 98107 cd/sqm



TEST NUMBER: P772395

CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	689.9	8.6
10°-20°	1889.1	23.5
20°-30°	2309.2	28.7
30°-40°	1873.6	23.3
40°-50°	933.7	11.6
50°-60°	260.4	3.2
60°-70°	59.2	0.7
70°-80°	15.4	0.2
80°-90°	3.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4888.2	60.8
0°-40°	6761.8	84.2
0°-60°	7955.9	99.0
0°-90°	8034.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8034.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7295	
5°	7249	690
15°	6806	1889
25°	5066	2309
35°	3018	1874
45°	1188	934
55°	267	260
65°	57	59
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P772395

CATALOG NUMBER: LD6D80BD010-EU6DR6570959027-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	7295.0
2.5°	7289.7
5°	7248.9
7.5°	7225.4
10°	7160.0
12.5°	7027.0
15°	6806.2
17.5°	6461.0
20°	6027.9
22.5°	5560.5
25°	5066.3
27.5°	4537.8
30°	4026.5
32.5°	3521.6
35°	3017.7
37.5°	2514.9
40°	2036.8
42.5°	1588.7
45°	1187.8
47.5°	827.6
50°	562.8
52.5°	388.1
55°	266.9
57.5°	180.1
60°	122.2
62.5°	84.7
65°	56.8
67.5°	28.9
70°	19.3
72.5°	18.2
75°	16.1
77.5°	10.7
80°	7.5
82.5°	5.4
85°	3.2
87.5°	2.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)