

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774813

Luminaire Tested: LD6D95BD010-EU6DR7070959027-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR7070959027-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10733.4 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774813

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P774813

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105	111	108	106	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94	105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84	99	92	87	83		90	85	82		87	84	81		85	82	79
4	95	87	81	76	93	86	80	76		83	78	75		81	77	74		79	76	73
5	89	80	74	69	88	79	73	69		78	72	68		76	71	68		74	70	67
6	84	75	68	63	83	74	68	63		72	67	63		71	66	62		69	65	62
7	80	69	63	58	78	69	62	58		67	62	58		66	61	57		65	61	57
8	75	65	58	54	74	64	58	54		63	57	53		62	57	53		61	56	53
9	71	61	54	50	70	60	54	50		59	53	50		58	53	49		57	53	49
10	67	57	50	46	66	56	50	46		55	50	46		55	50	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	925635
5°	923325
10°	921320
15°	921062
20°	912056
25°	856767
30°	763806
35°	608986
40°	404370
45°	241759
50°	125326
55°	65872
60°	23294
65°	388
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 241759 cd/sqm



TEST NUMBER: P774813

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	800.6	7.5
10°-20°	2296.1	21.4
20°-30°	3239.1	30.2
30°-40°	2796.2	26.1
40°-50°	1252.2	11.7
50°-60°	327.8	3.1
60°-70°	21.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6335.8	59.0
0°-40°	9132.1	85.1
0°-60°	10712.1	99.8
0°-90°	10733.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10733.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8472	
5°	8418	801
15°	8143	2296
25°	7107	3239
35°	4566	2796
45°	1565	1252
55°	346	328
65°	2	21
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774813

CATALOG NUMBER: LD6D95BD010-EU6DR7070959027-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8471.8
2.5°	8462.6
5°	8418.5
7.5°	8381.9
10°	8304.2
12.5°	8234.1
15°	8142.7
17.5°	8037.6
20°	7844.1
22.5°	7525.7
25°	7106.8
27.5°	6620.8
30°	6054.1
32.5°	5360.9
35°	4565.7
37.5°	3688.2
40°	2835.1
42.5°	2154.1
45°	1564.6
47.5°	1078.6
50°	737.3
52.5°	508.8
55°	345.8
57.5°	208.7
60°	106.6
62.5°	33.5
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)