

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774123

Luminaire Tested: LD6D95BD010-EU6DR2570959030-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR2570959030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8846.6 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774123

CATALOG NUMBER: LD6D95BD010-EU6DR2570959030-6LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P774123

CATALOG NUMBER: LD6D95BD010-EU6DR2570959030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3666037
5°	3414455
10°	2435626
15°	1434491
20°	892557
25°	489843
30°	224016
35°	84845
40°	38424
45°	23100
50°	9587
55°	6172
60°	4305
65°	2921
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23100 cd/sqm



TEST NUMBER: P774123

CATALOG NUMBER: LD6D95BD010-EU6DR2570959030-6LBPD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2675.5	30.2
10°-20°	3623.8	41.0
20°-30°	1917.7	21.7
30°-40°	473.4	5.4
40°-50°	115.5	1.3
50°-60°	30.4	0.3
60°-70°	10.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8217.0	92.9
0°-40°	8690.4	98.2
0°-60°	8836.2	99.9
0°-90°	8846.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8846.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	33553	
5°	31132	###
15°	12682	3624
25°	4063	1918
35°	636	473
45°	150	116
55°	32	30
65°	11	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774123

CATALOG NUMBER: LD6D95BD010-EU6DR2570959030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	33553.1
2.5°	33001.7
5°	31131.6
7.5°	27374.5
10°	21953.2
12.5°	16595.3
15°	12681.7
17.5°	9883.6
20°	7676.4
22.5°	5757.0
25°	4063.2
27.5°	2724.8
30°	1775.6
32.5°	1080.3
35°	636.1
37.5°	389.3
40°	269.4
42.5°	205.9
45°	149.5
47.5°	90.3
50°	56.4
52.5°	40.9
55°	32.4
57.5°	25.4
60°	19.7
62.5°	15.5
65°	11.3
67.5°	4.2
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)